




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Board, Wire-to-Wire**

Number of Positions: **6**

Centerline (Pitch): **6.35 mm [.25 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board, Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	6
Number of Rows	2

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Multiple Contact Types	Without
Contact Layout	Matrix
Contact Retention Within Housing	Without



Contact Type	Socket
Termination Features	
Termination Method to Wire & Cable	Crimp
Mechanical Attachment	
Panel Mount Feature	Without
Connector Mounting Type	Cable Mount (Free-Hanging)
Housing Features	
Centerline (Pitch)	6.35 mm[.25 in]
Housing Color	Natural
Housing Material	Nylon
Dimensions	
	.8 in
Row-to-Row Spacing	6.35 mm[.25 in]
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operation/Application	
Circuit Application	Power & Signal
Industry Standards	
CSA Rating	Certified, LR 7189
UL Rating	Recognized
Compatible With Agency/Standards Products	CSA, UL, VDE
Compatible With Approved Standards Products	UL E28476
UL Flammability Rating	UL 94V-2
Glow Wire Rating	Standard Part - Not Glow Wire
Packaging Features	
Packaging Quantity	1
Packaging Method	Package
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant




EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 350431-4 06P UMNL PINHDR ASSY V2 NAT LF	 TE Part # 640309-6 UMNL PIN 12-10 AU/PHBZ	 TE Part # 350690-2 UMNL PIN 24-18 AUBR L/P	 TE Part # 350762-5 06P UMNL HDR ASSY PC LF
 TE Part # 926902-3 UNIV-MNL SPLIT ST	 TE Part # 350550-7 UMNL SOK 20-14 AU/BR L/P	 TE Part # 350690-3 UMNL PIN 24-18 PTPPHBZ L/P	 TE Part # 350689-7 UMNL SOK 24-18 AUBR L/P



TE Part # 350547-7
UMNL PIN 20-14 AUBR L/P



TE Part # 350585-1
06P UMNL PIN HDR ASSY V2 NATL



TE Part # 350689-2
UMNL SOK 24-18 AUBR L/P



TE Part # 640310-3
UMNL SOK 12-10 PTPPHBZ



TE Part # 350689-3
UMNL SOK 24-18 PTPPHBZ L/P



TE Part # 350690-7
UMNL PIN 24-18 AUBR L/P



TE Part # 350689-1
UMNL SOK 24-18 PTPBR L/P



TE Part # 926893-3
UNIV.M-N-L.SOCKET



TE Part # 350550-6
UMNL SOK 20-14 AU/PHBZ L/P



TE Part # 350705-7
UMNL SPLIT PIN 20-14 AUBR L/P



TE Part # 350547-3
UMNL PIN 20-14 PTPPHBZ L/P



TE Part # 350551-7
UMNL SOK 20-14 AU/BR L/P

Also in the Series | Universal MATE-N-LOK



Circular Power Connectors(2)



Connector Caps & Covers(34)



Connector Contacts(209)




Connector Hardware(12)



Connector Seals & Cavity Plugs(27)



Connector Strain Relief(7)



Insertion & Extraction Tools(4)



Rectangular Connector Housings(1)



Rectangular Power Connectors(672)


Customers Also Bought



TE Part #1586860-1
06P UMNL CAP HSG, GW




TE Part #927231-7
UMNL 9 WAY CAP HOUSING



TE Part #794993-1
06P UMNL BLACK INTERFACE SEAL



TE Part #62002-2
SPLC AMVAR 7000-13000 025TPBR




TE Part #62310-2
AMVAR SPLC 7000-13000 025TPBR



TE Part #5-103961-4
4X5 MTE RCPT SR LATCH .100CL



TE Part #5-103974-4
4X5 MTE RCPT SR PLAIN .100CL



TE Part #53032-1
BUDGET SPRING SPADE 16-14 1/4



TE Part #794270-1
02P UMNL WIRE SEAL



TE Part #350925-1
UMNL SOK 30-26 PTPBR

Documents

Product Drawings

06P UMNL PLUG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_794096-1_F.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_794096-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_794096-1_F.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Product Specifications

[Application Specification](#)

English