




Free Height

TE Internal #: 1-5316318-1
PCB Mount Receptacle, Vertical, Board-to-Board, 160 Position, .6 mm [.024 in] Centerline, Gold, Surface Mount, Signal, Black, Free Height
[View on TE.com >](#)

Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**
PCB Mount Orientation: **Vertical**
Connector System: **Board-to-Board**
Number of Positions: **160**
Centerline (Pitch): **.6 mm [.024 in]**

Features

Product Type Features

Ground Feature Type	Grounding Contact, Grounding Plate
PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Stackable	Yes
PCB Mount Orientation	Vertical
Number of Positions	160
Board-to-Board Configuration	Parallel

Electrical Characteristics

Dielectric Withstanding Voltage (Max)	200 VAC
Insulation Resistance	2 MΩ
Operating Voltage	50 VAC

Body Features



Primary Product Color	Black
-----------------------	-------

Contact Features

PCB Contact Termination Area Plating Material Thickness	1 µm[39.37 µin]
Contact Layout	Inline
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Thickness	.2 µm[7.874 µin]
Contact Type	Socket
Contact Current Rating (Max)	.5 A

Termination Features

Rectangular Termination Post & Tail Thickness	.15 mm[.006 in]
Rectangular Termination Post & Tail Width	.9 mm[.035 in]
Termination Method to Printed Circuit Board	Surface Mount

Mechanical Attachment

PCB Mount Alignment Type	Locating Posts
PCB Mount Retention Type	Solder Peg
Mating Alignment	With
Mating Alignment Type	Polarization
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	.6 mm[.024 in]
Housing Material	High Temperature Thermoplastic

Dimensions

Connector Height	12 mm[.472 in]
Stack Height	12 mm, 13 mm, 14 mm, 15 mm, 16 mm, 18 mm[.709 in]
	.2 in

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------



Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	30
Packaging Type	Tray

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-5316559-1
[.6FHP04H,160,S,GIG,08/Sn,HT,SEYes](#)

TE Part # 1-5316562-1
[.6FHP08H,160,S,GIG,08/Sn,ST,NS](#)

TE Part # 1-5353188-1
[.6FHP08H,160,S,GIG,08/Sn,TR,NSYes](#)

TE Part # 1-5316135-0
[.6FHP04H,140,S,STD,08/Sn,ST,NSYes](#)

TE Part # 1-5353185-0
[.6FHP06H,140,S,STD,08/Sn,TR,NSYes](#)

TE Part # 1-5353187-0
[.6FHP08H,140,S,STD,08/Sn,TR,NSYes](#)

TE Part # 1-5353188-0
[.6FHP08H,140,S,GIG,08/Sn,TR,NSYes](#)

TE Part # 1-5316316-0
[.6FHP08H,140,S,GIG,08/Sn,HT,SEYes](#)

TE Part # 1-5316559-0
[.6FHP04H,140,S,GIG,08/Sn,HT,SEYes](#)

TE Part # 1-5316562-0
[.6FHP08H,140,S,GIG,08/Sn,ST,NSYes](#)

TE Part # 1-5353184-0
[.6FHP04H,140,S,GIG,08/Sn,TR,NSYes](#)

TE Part # 1-5353186-0
[.6FHP06H,140,S,GIG,08/Sn,TR,NSYes](#)

TE Part # 1-5353186-1
[.6FHP06H,160,S,GIG,08/Sn,TR,NSYes](#)

TE Part # 1-5353831-0
[.6FHP07H,140,S,GIG,08/Sn,TR,NS](#)

TE Part # 1-6123582-1
[.6FHP10H,160,S,GIG,08/Sn,ST,NSYes](#)

TE Part # 1-6376014-1
[.6FHP10H,160,S,STD,08/Sn,ST,NSYes](#)

TE Part # 6-5316562-0
[.6FHP08H,140,S,GIG,08/Sn,ST,SEYes](#)

TE Part # 6-5353184-0
[.6FHP04H,140,S,GIG,08/Sn,TR,SEYes](#)

TE Part # 6-5353188-0
[.6FHP08H,140,S,GIG,08/Sn,TR,SEYes](#)

TE Part # 6318453-8
[.6FHP11H,100,S,STD,08/Sn,ST,NSYes](#)

Also in the Series | [Free Height](#)



Customers Also Bought



Documents

Product Drawings
.6FHR12H,160,S,GIG,08/Sn,HT,SEYes
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1-5316318-1_B1.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1-5316318-1_B1.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1-5316318-1_B1.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

Fine Pitch Stacking Connectors - 0.6mm Free Height (FH) and GIGA Connectors

English

Product Specifications

Application Specification

English