

Specification Sheet

Part Number: RT50S0C2



Special extended-pawl design offers a release feature for quick and easy access to wire bundles.

Head design provides high tensile strength with very low insertion force even after repeated use.

Bent tail ensures a quick and simple installation.

Releasable Cable Tie, Release Tab, 6.5" Long, 50 lb Tensile Strength, PA66, Black, 100/pkg

Article Number	115-06300
----------------	-----------

Type	RT50S
------	-------

Color	Black (BK)
-------	------------

Quantity Per	bag
--------------	-----

Product Description	HellermannTyton Releasable Cable Ties feature an extended pawl for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use, as well as a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation.
---------------------	---

Short Description	Releasable Cable Tie, Release Tab, 6.5" Long, 50 lb Tensile Strength, PA66, Black, 100/pkg
-------------------	--

Global Part Name	RT50S-PA66-BK
------------------	---------------

Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	6.3
Length L (Metric)	160.0
Fixation Method	Releasable Cable Tie
Identification Plate Position	none
Releasable Closure	Yes
Tie Closure	plastic pawl
Variant	Inside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.5
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Height H (Imperial)	.06

Height H (Metric)	1.40
Material	Polyamide 6.6 (PA66)
Material Shortcut	PA66
Flammability	UL 94 V-2
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	UL-ZODZ2.E64139
UL Recognized (US)	Yes
UL Recognized (US and Canada)	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)