

Tel: 1-800-722-8197 1-631-595-2217 Fax: 1-631-667-5484 EMAIL: sales@challelec.com WEB: www.challengeelectronics.com ISO 9001/14001:2015 Certified

INDICATORS • SPEAKERS • SOUND TRANSDUCERS • ENCLOSURES • MICROPHONES • BATTERY ACCESSORIES

CS18-02P110-03-1X

Rev. 1-2022 RoHS3 & REACH IP67 Front Face Mobile Speakers




Operating Characteristics

ELECTRICAL

Rated Power	2 W	
Short Term Max Power	2.2 W	
Impedance	4 Ω ± 20 % 2000 Hz; 2 W	

ACOUSTIC: 1cc Sealed Enclosure

1100 Hz ± 20 %	
1100 to 20000 Hz	
104 ± 3 dB 1000, 1500, 2000 Hz; 2 W; 10 cm; Max 10 % 2000 Hz; 2 W	



Physical Characteristics


MAT	TER	ΔΙς	19


Housing	Plastic
Cone	PEEK
Magnet	NdFeB
Solder Pads	Tin Plated Stainless Steel


TEMPERATURE RANGES

Operating	-20 to +60 °C
Storage	-20 to +70 °C

Weight 3.5 g







General tolerance = ±0.2 mm and all measurements in mm unless otherwise noted.

Revision	Description	Ву	Date
0-2022	Original Specification	CT	2022-02-03
1-2022	Added minimum diaphragm clearance requirement callout to the mechanical drawing. Added product photo.	CT	2022-05-12

Warranty: For a period of one (1) year from date of shipping under normal operations conditions. This warranty does not apply to products damaged through misuse, abuse, improper installation, alteration, rework, or attempt to repair.

The information contained herein is believed to be correct, but no guarantee or warranty, express or implied, with respect to accuracy, completeness or results is extended and no liability is assumed. Challenge Electronics reserves the right to make changes in any specification, data or material contained herein.