




- 1.电路CIRCUIT: ON/OFF;
- 2.额定值RATING:16A 125/250VAC (UL;C-UL);
12A 125/250VAC (UL;C-UL);
16(4)A 250V~T125/55(ENEC17;NEMKO;CQC;CB)
16A (浪涌电流 130A) 125VAC 寿命10000次;
- 3.接触电阻 CONTACT RESISTANCE : <50mΩ
- 4.绝缘阻抗 INSULATION RESISTANCE : >100MΩ
(500VDC BETWEEN OPEN CONTACTS)
- 5.耐电压 DIELECTRIC STRENGTH : >1500VAC 0.5mA 1 MINTUTE
- 6.所有部件均使用环保材料
ALL MATERIALS USING MEET THE RoHS DIRECTIVE




TEL:0769-82310511-867



PANEL CUTOUT DIMENSION



PANEL THICKNESS	X	Y
0.8~1.2mm	19.2 ⁺⁰ _{-0.1} mm	12.9 ^{+0.1} ₋₀ mm
1.3~2.0mm	19.4 ⁺⁰ _{-0.1} mm	12.9 ^{+0.1} ₋₀ mm
2.1~2.5mm	19.8 ⁺⁰ _{-0.1} mm	12.9 ^{+0.1} ₋₀ mm



5	→	10	→	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN	MM			
4	→	9	→	RANGE	TOLERANCE				LMC 2020.11.14	SCALE	NO		DRAWING NO.	REV.
3	→	8	→	X	±0.30					MAT'L	***			
2	→	7	→	X.X	±0.20					MATERIAL NO.				
1	→	6	→	X.XX	±0.10					SS11-BBIWP-R20-L				
NO	DESCRIPTION	NO	DESCRIPTION	ANGLES	±1°	LEGION ELECTRONIC & HARDWARE CO., LTD.				WIF121045		A0		