

4



3

2




1

- 1.电路CIRCUIT: ON/OFF;  
2.快插端子QUICK CONNECTOR TYPE;  
单刀单掷(SINGLE POLE DOUBLE THROW);  
3.额定值RATING: 20A 125VAC  
16A 125/250VAC (UL;C-UL);  
12A 125/250VAC (UL;C-UL);  
16(4)A 250V~T125/55(ENEC17;NEMKO;CQC;CB)  
4.柄的颜色ACTUATOR COLOR: 黑色BLACK  
基座的颜色HOUSING COLOR: 黑色BLACK  
5.柄的印字形式ACTUATOR PRINTING: 白色"O/-" WHITE COLOR  
6.所有部件均使用环保材料  
ALL MATERIALS USE IN CONFORMIY WITH THE RoHS DIRECTIVE

## SCHEMATIC



PANEL CUTOUT DIMENSION,PANEL THICKNESS 0.8~1.2mm



|    |             |    |             |                        |           |                                        |         |        |       |                   |  |             |  |      |
|----|-------------|----|-------------|------------------------|-----------|----------------------------------------|---------|--------|-------|-------------------|--|-------------|--|------|
| 5  | →           | 10 | →           | DIMENSIONAL TOLERANCES |           | APPROVED                               | CHECKED | DESIGN | DRAWN | ALL SIZE ARE IN   |  | MM          |  |      |
| 4  | →           | 9  | →           | RANGE                  | TOLERANCE |                                        |         |        |       | SCALE             |  | NO          |  |      |
| 3  | →           | 8  | →           | X                      | ±0.30     |                                        |         |        |       | MAT'L             |  | ***         |  |      |
| 2  | →           | 7  | →           | X.X                    | ±0.20     |                                        |         |        |       | MATERIAL NO.      |  | DRAWING NO. |  | REV. |
| 1  | →           | 6  | →           | X.XX                   | ±0.10     |                                        |         |        |       | SS11-BBIWG-RR20-R |  | WIF120089   |  | A0   |
| NO | DESCRIPTION | NO | DESCRIPTION | ANGLES                 | ±1°       | LEGION ELECTRONIC & HARDWARE CO., LTD. |         |        |       |                   |  |             |  |      |

4

3

2

1