


### 3. ELECTRICAL SPECIFICATIONS

TEST CONDITION ( Vs=1.5V,RL=2.2KOHM TEMP= $22\pm3$  °C,R.H.=  $50\sim70\%$ )

			٠			
ITEM	SYMBOL	SYMBOL TEST CONDITION	<u>N</u>	STANDARD MAX	MAX.	TINU
SENSITIVITY ***	SENS	f = 1KHz	<b>-</b> 63	-60	-57	dB 0dB=1V/ubar
DIRECTIVITY		OMNI-DIRECTIONAL	TIONAL			
IMPEDANCE	Zout				2.2	KOhm
MAX. SOUND PRESSURE LEVEL	S.P.L				100	dB
OPERATION VOLTAGE	٧s		1.0	1.5	10	<b>V</b>
OPERATION CONSUMPTION	_				0.45	mA
SENSITIVITY REDUCTION	S∆	f=1KHz Vs=1.5~1.0V		S▽		dB 0dB=1V/ubar
S/N RATIO	S/A	f=1KHz	60			dB 0dB=1V/ubar

#### REV. "A"


# 5. TYPICAL FREQUENCY RESPONSE CURVE:




6. AMBIENT CONDITION:

- (1) OPERATING CONDITION: AMBIENT TEMPERATURE: -10  $^{\circ}$ -+45 $^{\circ}$
- (2) STORAGE CONDITION: AMBIENT TEMPERATURE: -25  $^{\sim}$  +60  $^{\circ}$  RELATIVE HUMIDITY:  $\leqslant$  75%

### 4. MEASUREMENT CIRCUIT:



### NOTE: ALL DIMS ARE IN mm



08-250 ECN#

SYM A

07/11/08 DATE

CHANGED THE DRAWING TO NEW PRINT

REVISION RECORD

## 7. MECHANICAL CHARACTERISTICS

_	
ERMINAL MECHANICAL	WEIGHT
TO BE NO INTERFERE IN OPERATION AFTER PULLED THE	LESS THAN: 1.0g
	RMINAL MECHANICAL TO BE NO INTERFERE IN OPERATION AFTER PULLED T

#### 8. RELIABILITY TESTS

HUMIDITY  AFTER EXPOSURE AT 40°C.  HUMIDITY FOR 48 HOURS, 19 FROM INITIAL SENSITIVITY.	LOW TEMPERATURE  BE WITHIN ±3dB FROM INITIAL SENSITIVITY.  (THE MEASUREMENT TO BE DONE AFTER 3  CONDITIONING AT 20°C)	HIGH TEMPERATURE  BE WITHIN ±3dB FROM INITIAL SENSITIVITY  (THE MEASUREMENT TO BE DONE AFTER 3  CONDITIONING AT 20°C)	DROP TEST  TO BE NO INTERFERE IN CONCRETE FLOOR EACH HEIGHT AT THREE DIRECT SENSITIVITY TO BE WIT	VIBRATION TEST  TO BE NO INTERFERE IN TO 55Hz FOR 1 MINUTE F TO BE WITHINN +/-3dB F(	SOLDERING HEAT SHOCK TO BE NO INTERFERE IN HEAT SHOCK, TEMPERAN SENSITIVITY TO BE WITH	
AFTER EXPOSURE AT 40 °C±2°C AND 90~ 95% RELATIVE HUMIDITY FOR 48 HOURS, SENSITIVITY TO BE WITHIN ±3dB FROM INITIAL SENSITIVITY.  (THE MEASUREMENT TO BE DONE AFTER 3 HOURS OF	AFTER EXPOSURE AT -40°C FOR 48 HOURS, SENSITIVITY TO BE WITHIN ±3dB FROM INITIAL SENSITIVITY. (THE MEASUREMENT TO BE DONE AFTER 3 HOURS OF CONDITIONING AT 20°C)	AFTER EXPOSURE AT 70±2°C FOR 48 HOURS, SENSITIVITY TO BE WITHIN ±3dB FROM INITIAL SENSITIVITY. (THE MEASUREMENT TO BE DONE AFTER 3 HOURS OF CONDITIONING AT 20°C)	TO BE NO INTERFERE IN OPERATION AFTER DROPPED TO CONCRETE FLOOR EACH ONE TIME FROM 1 METER HEIGHT AT THREE DIRECTIONS IN STATE OF PACKING. SENSITIVITY TO BE WITHINN +/-3dB FORM INITIAL SENSITIVITY	TO BE NO INTERFERE IN OPERATION AFTER VIBRATION 10Hz TO 55Hz FOR 1 MINUTE FULL AMPLITUDE 0.55mm. SENSITIVITY TO BE WITHINN +/-3dB FORM INITIAL SENSITIVITY	TO BE NO INTERFERE IN OPERATION AFTER SOLDERING HEAT SHOCK, TEMPERATURE 320°C±20°C FOR 1~3 SECONDS. SENSITIVITY TO BE WITHINN +/-3dB FORM INITIAL SENSITIVITY	


			CYCLE TEST	TEMPERATURE
(THE MEASUREMENT TO BE DONE AFTER 3	INITIAL SENSITIVITY.	SENSITIVITY TO BE WITHIN ±3dB FROM	AT 40℃ FOR 2 HOURS, WITH 10 CYCLES,	AFTER EXPOSURE AT -20±3℃ FOR 2 HOURS,

HOURS OF CONDITIONING AT 20°C)

#### 9. CAUTIONS

- 1) TEH TEMPERATURE OF THE WORKING SURFACE OF THE SOLDERING COPPER SHALL BE BELOW  $320\#\pm20\,\%$
- ECM SHALL BE SOLDERED FIXED ON THE METAL BLOCK(HEAT SINK)
  WHICH HAS THE HIGHER RADIATION EFFECTS SAID HEAT SINK SHALI
  CONTACT WITH EACH OF ECM.
- 3) THE SOLDERING TIME FOR EACH TERMINAL SHALL BE 1~3 SECONDS
- 4) ECM MAY EASILY DESTROYED BY THE STATIC ELECTRICITY, AND THE COUNTERMEASURE FOR ELIMINATION THE STATIC ELECTRICITY(THE GROUND OR SOLDERING COPPING COPPER, FOR WORKTABLE AND FOR HUMAN BOADY) SHALL BE EXECUTED

NOTE: ALL DIMS ARE IN mm



08-250 ECN#

SYM A

07/11/08 DATE


CHANGED THE DRAWING TO NEW PRINT

REVISION RECORD

### 10. PACKING SPECIFICATION:

OUTER BOX	PACKING	
		DRAWING
5,000 (10X500)	500	QTY(PCS)
230X230X260	212.5X103X48	SIZE(mm)
PAPER	PAPER	REMARK

### NOTE: ALL DIMS ARE IN mm



08-250 ECN#

S X P

07/11/08 DATE