

Remarks:


- 1、Do not cut off copper wire when cutting wire.
- 2、Do not burn wire when baking heat-shrink tube.
- 3、Pull-force of terminal should reach the standard.
- 4、Hook/clasp the wire and solder with terminal of socket.

Test condition

1. Short/open circuit: 100% test


TEL: 0769-82310511-867

序号	名称	数量	规格
1	AC插座	1	RT-C14-L00B-AA 10A/15A 250VAC
2	热缩套管	2	黑色热缩套管 L=15mm
3	线材	1	UL3385 18AWG 颜色: 棕色线
4	线材	1	UL3385 18AWG 颜色: 黄注绿条线
5	线材	1	UL3385 18AWG 颜色: 蓝色线
6	热缩套管	1	黑色热缩套管
7	圆环端子	1	∅7.5*ID4.0*T0.4mm 镀锡端子
8	胶壳	1	3.96-3Y/8639-03 白色胶壳
9	端子	2	3.96-T/8478 镀锡端子
10	热缩套管	2	黑色热缩套管 L=30mm



标签要求:

- 1、尺寸: 不做限定, 满足排版美观即可。
- 2、材质: PET(-40℃/149℃)亚膜
- 3、特性要求:
 - a: 丝印附着力合格
 - b: 扫描识别度小于1秒, 无卡顿
- 4、内容要求:
 - 明码: 物料编号+供应商代码+年月日+流水号



物料编码: 84503039 供应商代码: 10334 年月日: 220608 流水号: 每个标签由00001, 00002...依次连号下去

焊接(钩焊)示意图	Wiring table		
	P1	P2	P3
	N Blue	1	
	E Yellow/Green		RING TERMINAL
	L Brown	3	

NO	DESCRIPTION	NO	DESCRIPTION	DIMENSIONAL TOLERANCES		APPROVED	CHECKED	DESIGN	DRAWN	ALL SIZE ARE IN		DRAWING NO.	REV.
				RANGE	TOLERANCE					MM	NO		
5		10											
4		9											
3		8		X	±0.30				LMC				
2	修改标签 2022.05.26	7		X.X	±0.20				2021.06.11				
1	52 → 67 2022.04.12	6		X.XX	±0.10								
				ANGLES	±1'	ROCKTEK ELECTRICAL(SHENZHEN) CO.,LTD.				RT-C14-L00B-AA-34	WIF122013	A2	