


REVERSE VOLTAGE: 30 - 200 V
FORWARD CURRENT: 2.0 A



Features

- ✧ Schottky barrier rectifier
- ✧ Guardring protection
- ✧ Low forward voltage
- ✧ Reverse energy tested
- ✧ High current capability
- ✧ Extremely low thermal resistance

Mechanical Data

- ✧ Case: SMA molded plastic body
- ✧ Polarity: Color band denotes cathode end
- ✧ Mounting position: ANY
- ✧ Weight: 0.002 ounces, 0.064 gram

SMA/DO-214AC



Dimensions in inches and(millimeters)





MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25 C ambient temperature unless otherwise specified

		BR23	BR24	BR25	BR26	BR28	BR29	BR210	BR215	BR220	UNITS
Maximum repetitive peak reverse voltage	V _{RRM}	30	40	50	60	80	90	100	150	200	V
Maximum RMS voltage	V _{RWS}	21	28	35	42	56	63	70	105	140	V
Maximum DC blocking voltage	V _{DC}	30	40	50	60	80	90	100	150	200	V
Maximum average forward rectified current at T _L =90	I _{F(AV)}	2.0									A
Peak forward surge current 8.3ms single half-sine-wave	I _{FSM}	50									A
Maximum instantaneous forward voltage at I _{FM} =2.0A (NOTE1)	V _F	0.7	0.75				0.80			V	
Maximum DC reverse current T _J =25℃ at rated DC blocking voltage T _J =125℃	I _R	0.05 15									m A
Maximum thermal resistance	R _{θJL}	28									℃/W
Operating temperature range	T _J	-55 ---- +150									℃
Storage temperature range	T _{STG}	-55 ---- +175									℃

NOTE: 1.Pulse test: Pulse width 300us,duty cycle 1 %

Ratings AND Characteristic Curves

FIG.1 – FORWARD DERATING CURVE

FIG.2– PEAK FORWARD SURGE CURRENT

FIG.3 – TYPICAL FORWARD CHARACTERISTICS

FIG.4 – TYPICAL REVERSE CHARACTERISTICS


PACKAGE	SPQ/PCS	CARTON SPQ/PCS	CARTON SIZE/CM	CARTON GW/KG	CARTON NW/KG
SMA	5000/REEL	80000	36X30.6X31	12.00	11.00