




Connectors > Contacts > Connector Contacts



Contact Type: **Pin**

Contact Mating Area Plating Material: **Gold**

Wire Contact Termination Area Plating Material: **Pre-Tin**

Operating Voltage: **600 VAC**

Contact Retention Within Housing: **With**

Features

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Mating Square Post Dimension	1.14 mm[.045 in]
Contact Fabrication	Stamped & Formed
Contact Underplating Material Thickness	1.27 µm[50 µin]
Wire Contact Termination Area Plating Thickness	2.54 µm[100 µin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Orientation	Straight
Contact Underplating Material	Nickel
Contact Type	Pin
Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Pre-Tin
Contact Retention Within Housing	With
Contact Base Material	Brass



Contact Current Rating (Max)	9 A
Termination Features	
Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable
Mechanical Attachment	
Wire Insulation Support	Without
Dimensions	
Compatible Insulation Diameter Range	1.19 – 1.75 mm[.047 – .069 in]
Wire Size	.13 – .33 mm²
Usage Conditions	
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
Operation/Application	
Circuit Application	Power
Industry Standards	
Compatible With Agency/Standards Products	CSA, UL
Packaging Features	
Packaging Quantity	5000
Packaging Method	Reel
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2238022-1 VAL-U-LOK PIN BR SN 26-22 LP	 TE Part # 2266139-1 OCEAN-2.0-APPLICATOR-S-055F070F	 TE Part # 2266139-2 OCEAN-2.0-APPLICATOR-S-055F070FA	 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp
 TE Part # 2836282-1 OCEAN_2.0_Applicator-S-055F062F	 TE Part # 2836282-2 OCEAN_2.0_Applicator-S-055F062F	 TE Part # 7-2266139-1 OCEAN-2.0-APPLICATOR-S-055F070F	 TE Part # 7-2266139-2 OCEAN-2.0-APPLICATOR-S-055F070FA
 TE Part # 7-2266139-7 OCEAN_2.0_SPARE_PART_KIT-055F070F	 TE Part # 7-2836282-1 OCEAN_2.0_Applicator-S-055F062F	 TE Part # 7-2836282-2 OCEAN_2.0_Applicator-S-055F062F	 TE Part # 7-2836282-7 OCEAN_2.0_SPARE_PART_KIT-055F062F
 TE Part # 91387-2 PRO-CRIMPER DIE(ONLY)			



Customers Also Bought



TE Part #206429-1
CPC PLUG ASSY, 11-4, REV SEX




TE Part #1-66099-5
III+ PIN,18-16,TIN ,LP




TE Part #1971795-1
NEW GI CONN2.5 REC. CONTACT




TE Part #193846-1
SKT ASSY.



TE Part #1586018-4
4P PM PLUG VAL-U-LOK V0



TE Part #282834-2
TERMI-BLOK PCB MOUNT, 90 2P.



TE Part #794953-2
2P PM PLUG VAL-U-LOK V2



TE Part #1-2834021-3
3POS 2.5MM TES CONN.

TE Part #098-10125
ML SENSOR 316SS STANDARD

Documents

Product Drawings

VAL-U-LOK PIN BR AU 22-26AWG

English

CAD Files

Customer View Model

ENG_CVM_CVM_794957-2_E.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_794957-2_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_794957-2_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

SOFT_SHELL_PIN_AND_SOCKET_CONNECTORS_CATALOG

English

Product Specifications

Application Specification

English