




A-CODE FEMALE INTERFACE

POLE	02	03	04	05	06	07	08
PIN SIZE "A"	0.8mm	0.8mm	0.8mm	0.8mm	0.8mm	0.8mm	0.8mm
RATED VOLTAGE	250V	250V	250V	60V	30V	30V	30V
RATED CURRENT	4A	4A	4A	4A	2A	2A	2A
RATED IMPULSE VOLTAGE	2.5KV	2.5KV	2.5KV	1.5KV	0.8KV	0.8KV	0.8KV



RECOMMENDED PCB LAYOUT

- NOTE:
- ELECTRICAL:
 - CONTACT RESISTANCE: $\leq 15\text{m}\Omega$
 - INSULATION RESISTANCE: $\geq 100\text{M}\Omega$
 - ENVIRONMENTAL:
 - OPERATING TEMPERATURE: -25°C TO $+85^{\circ}\text{C}$
 - PROTECTION GRADE: IP67, WHEN TIGHT LOCKED
 - POLLUTION DEGREE: 3
 - CONTACT MATERIAL: BRASS NI PLATED UNDER GOLD PLATED
 - CONFORM TO IEC 61076-2-101



PANEL CUT OUT

* UNLESS OTHERWISE SPECIFIED
TOLERANCES ON DECIMAL IS:
X. ± 0.50 X° $\pm 2^{\circ}$
X.X ± 0.30
X.XX ± 0.20

		Material:				
		Finishing:				
Created by	Signature	Date	Phase Marking		Weight	Scale
						1:1
Checked by			P/N		61018007	
Approved by			MD/CD			
State	First Release				Rev.	Page:
					01	1 OF 1

Mark	Qty	Engineering Change Area

拓宜(上海)工控电器设备有限公司
Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.

Part Name:
C12B-FSA-RM1-8

Rev.
01

Page:
1 OF 1