



# Optocoupler, Phototransistor Output, High Reliability, 5300 V<sub>RMS</sub>



## DESCRIPTION

The SFH610A and SFH6106 feature a high current transfer ratio, low coupling capacitance and high isolation voltage. These couplers have a GaAs infrared diode emitter, which is optically coupled to a silicon planar phototransistor detector, and is incorporated in a plastic DIP-4 or SMD package.

The coupling devices are designed for signal transmission between two electrically separated circuits.

The couplers are end-stackable with 2.54 mm spacing.

Creepage and clearance distances of > 8.0 mm are achieved with option 6 and option 8. This version complies with IEC 60950 (DIN VDE 0805) for reinforced insulation up to an operation voltage of 400 V<sub>RMS</sub> or DC. Specifications subject to change.

## FEATURES

- Good CTR linearity depending on forward current
- Isolation test voltage, 5300 V<sub>RMS</sub>
- High collector emitter voltage, V<sub>CEO</sub> = 70 V
- Low saturation voltage
- Fast switching times
- Low CTR degradation
- Temperature stable
- Low coupling capacitance
- End stackable, 0.100" (2.54 mm) spacing
- High common mode interference immunity
- Material categorization: for definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT

## LINKS TO ADDITIONAL RESOURCES





## AGENCY APPROVALS

- [UL](#)
- [cUL](#)
- [DIN EN 60747-5-5 \(VDE 0804\)](#), available with option 1
- [BSI](#)
- [CQC](#)
- [FIMKO](#)



## ORDERING INFORMATION



| AGENCY CERTIFIED / PACKAGE               | CTR (%)                       |                               |                               |                               |            |
|------------------------------------------|-------------------------------|-------------------------------|-------------------------------|-------------------------------|------------|
| UL, cUL, BSI, FIMKO, CQC                 | 40 to 80                      | 63 to 125                     | 100 to 200                    | 160 to 320                    | 250 to 500 |
| DIP-4                                    | SFH610A-1                     | SFH610A-2                     | SFH610A-3                     | SFH610A-4                     | SFH610A-5  |
| DIP-4, 400 mil, option 6                 | -                             | SFH610A-2X006                 | SFH610A-3X006                 | -                             | -          |
| SMD-4                                    | SFH6106-1T <sup>(1)</sup>     | SFH6106-2T <sup>(1)</sup>     | SFH6106-3T <sup>(1)</sup>     | SFH6106-4T <sup>(1)</sup>     | SFH6106-5T |
| SMD-4, option 7                          | -                             | -                             | SFH610A-3X007T                | -                             | -          |
| SMD-4, 400 mil, option 8                 | -                             | -                             | -                             | SFH610A-4X008T                | -          |
| UL, cUL, BSI, FIMKO, CQC, VDE (option 1) | 40 to 80                      | 63 to 125                     | 100 to 200                    | 160 to 320                    | 250 to 500 |
| DIP-4                                    | SFH610A-1X001                 | SFH610A-2X001                 | SFH610A-3X001                 | SFH610A-4X001                 | -          |
| DIP-4, 400 mil, option 6                 | SFH610A-1X016                 | -                             | SFH610A-3X016                 | SFH610A-4X016                 | -          |
| SMD-4                                    | SFH6106-1X001T <sup>(1)</sup> | SFH6106-2X001T <sup>(1)</sup> | SFH6106-3X001T <sup>(1)</sup> | SFH6106-4X001T <sup>(1)</sup> | -          |
| SMD-4, 400 mil, option 8                 | SFH610A-1X018T                | -                             | -                             | -                             | -          |

## Notes

- For additional information on the available options refer to option information
- <sup>(1)</sup> Also available in tubes; do not add T to end

ABSOLUTE MAXIMUM RATINGS ( $T_{amb} = 25^{\circ}\text{C}$ , unless otherwise specified)

| PARAMETER                            | TEST CONDITION                                                           | SYMBOL     | VALUE       | UNIT               |
|--------------------------------------|--------------------------------------------------------------------------|------------|-------------|--------------------|
| input                                |                                                                          |            |             |                    |
| Reverse voltage                      |                                                                          | $V_R$      | 6           | V                  |
| DC forward current                   |                                                                          | $I_F$      | 60          | mA                 |
| Surge forward current                | $t \leq 10 \mu\text{s}$                                                  | $I_{FSM}$  | 2.5         | A                  |
| Power dissipation                    |                                                                          | $P_{diss}$ | 100         | mW                 |
| output                               |                                                                          |            |             |                    |
| Collector emitter voltage            |                                                                          | $V_{CEO}$  | 70          | V                  |
| Emitter collector voltage            |                                                                          | $V_{ECO}$  | 7           | V                  |
| Collector current                    | $t_p \leq 1.0 \text{ ms}$                                                | $I_C$      | 50          | mA                 |
|                                      |                                                                          | $I_c$      | 100         | mA                 |
| Power dissipation                    |                                                                          | $P_{diss}$ | 150         | mW                 |
| coupler                              |                                                                          |            |             |                    |
| Storage temperature range            |                                                                          | $T_{stg}$  | -55 to +150 | $^{\circ}\text{C}$ |
| Ambient temperature range            |                                                                          | $T_{amb}$  | -55 to +100 | $^{\circ}\text{C}$ |
| Soldering temperature <sup>(1)</sup> | Max. 10 s, dip soldering distance to seating plane $\geq 1.5 \text{ mm}$ | $T_{sld}$  | 260         | $^{\circ}\text{C}$ |

## Notes

- Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute maximum ratings for extended periods of the time can adversely affect reliability.
- <sup>(2)</sup> Refer to reflow profile for soldering conditions for surface mounted devices (SMD). Refer to wave profile for soldering conditions for through hole devices (DIP).



| ELECTRICAL CHARACTERISTICS (T <sub>amb</sub> = 25 °C, unless otherwise specified) |                                                 |           |                    |      |      |      |      |
|-----------------------------------------------------------------------------------|-------------------------------------------------|-----------|--------------------|------|------|------|------|
| PARAMETER                                                                         | TEST CONDITION                                  | PART      | SYMBOL             | MIN. | TYP. | MAX. | UNIT |
| INPUT                                                                             |                                                 |           |                    |      |      |      |      |
| Forward voltage                                                                   | I <sub>F</sub> = 60 mA                          |           | V <sub>F</sub>     | -    | 1.25 | 1.65 | V    |
| Reverse current                                                                   | V <sub>R</sub> = 6 V                            |           | I <sub>R</sub>     | -    | 0.01 | 10   | μA   |
| Capacitance                                                                       | V <sub>R</sub> = 0 V, f = 1 MHz                 |           | C <sub>O</sub>     | -    | 13   | -    | pF   |
| Thermal resistance                                                                |                                                 |           | R <sub>thja</sub>  | -    | 750  | -    | K/W  |
| OUTPUT                                                                            |                                                 |           |                    |      |      |      |      |
| Collector emitter capacitance                                                     | V <sub>CE</sub> = 5 V, f = 1 MHz                |           | C <sub>CE</sub>    | -    | 5.2  | -    | pF   |
| Thermal resistance                                                                |                                                 |           | R <sub>thja</sub>  | -    | 500  | -    | K/W  |
| Collector emitter leakage current                                                 | V <sub>CE</sub> = 10 V                          | SFH610A-1 | I <sub>CEO</sub>   | -    | 2    | 50   | nA   |
|                                                                                   |                                                 | SFH6106-1 | I <sub>CEO</sub>   | -    | 2    | 50   | nA   |
|                                                                                   |                                                 | SFH610A-2 | I <sub>CEO</sub>   | -    | 2    | 50   | nA   |
|                                                                                   |                                                 | SFH6106-2 | I <sub>CEO</sub>   | -    | 2    | 50   | nA   |
|                                                                                   |                                                 | SFH610A-3 | I <sub>CEO</sub>   | -    | 5    | 100  | nA   |
|                                                                                   |                                                 | SFH6106-3 | I <sub>CEO</sub>   | -    | 5    | 100  | nA   |
|                                                                                   |                                                 | SFH610A-4 | I <sub>CEO</sub>   | -    | 5    | 100  | nA   |
|                                                                                   |                                                 | SFH6106-4 | I <sub>CEO</sub>   | -    | 5    | 100  | nA   |
|                                                                                   |                                                 | SFH610A-5 | I <sub>CEO</sub>   | -    | 5    | 100  | nA   |
|                                                                                   |                                                 | SFH6106-5 | I <sub>CEO</sub>   | -    | 5    | 100  | nA   |
| COUPLER                                                                           |                                                 |           |                    |      |      |      |      |
| Collector emitter saturation voltage                                              | I <sub>F</sub> = 10 mA, I <sub>C</sub> = 2.5 mA |           | V <sub>CEsat</sub> | -    | 0.25 | 0.4  | V    |
| Coupling capacitance                                                              | f = 1 MHz                                       |           | C <sub>C</sub>     | -    | 0.4  | -    | pF   |

**Note**

- Minimum and maximum values are testing requirements. Typical values are characteristics of the device and are the result of engineering evaluation. Typical values are for information only and are not part of the testing requirements.

| <b>CURRENT TRANSFER RATIO</b> |                                                |            |        |      |      |      |      |
|-------------------------------|------------------------------------------------|------------|--------|------|------|------|------|
| PARAMETER                     | TEST CONDITION                                 | PART       | SYMBOL | MIN. | TYP. | MAX. | UNIT |
| $I_C/I_F$                     | $I_F = 10\text{ mA}$ , $V_{CE} = 5.0\text{ V}$ | SFH610A-1  | CTR    | 40   | -    | 80   | %    |
|                               |                                                | SFH6106-1  | CTR    | 40   | -    | 80   | %    |
|                               |                                                | SFH610A-2  | CTR    | 63   | -    | 125  | %    |
|                               |                                                | SFH6106-2  | CTR    | 63   | -    | 125  | %    |
|                               |                                                | SFH610A-3  | CTR    | 100  | -    | 200  | %    |
|                               |                                                | SFH6106-3  | CTR    | 100  | -    | 200  | %    |
|                               |                                                | SFH610A-4  | CTR    | 160  | -    | 320  | %    |
|                               |                                                | SFH6106-4  | CTR    | 160  | -    | 320  | %    |
|                               |                                                | SFH610A-5  | CTR    | 250  | -    | 500  | %    |
|                               |                                                | SFH6106-5T | CTR    | 250  | -    | 500  | %    |
|                               | $I_F = 1\text{ mA}$ , $V_{CE} = 5\text{ V}$    | SFH610A-1  | CTR    | 13   | 30   | -    | %    |
|                               |                                                | SFH6106-1  | CTR    | 13   | 30   | -    | %    |
|                               |                                                | SFH610A-2  | CTR    | 22   | 45   | -    | %    |
|                               |                                                | SFH6106-2  | CTR    | 22   | 45   | -    | %    |
|                               |                                                | SFH610A-3  | CTR    | 34   | 70   | -    | %    |
|                               |                                                | SFH6106-3  | CTR    | 34   | 70   | -    | %    |
|                               |                                                | SFH610A-4  | CTR    | 56   | 90   | -    | %    |
|                               |                                                | SFH6106-4  | CTR    | 56   | 90   | -    | %    |



| SWITCHING CHARACTERISTICS |                                              |           |                  |      |      |      |      |
|---------------------------|----------------------------------------------|-----------|------------------|------|------|------|------|
| PARAMETER                 | TEST CONDITION                               | PART      | SYMBOL           | MIN. | TYP. | MAX. | UNIT |
| NON-SATURATED             |                                              |           |                  |      |      |      |      |
| Current                   | V <sub>CC</sub> = 5 V, R <sub>L</sub> = 75 Ω |           | I <sub>F</sub>   | -    | 10   | -    | mA   |
| Rise time                 | V <sub>CC</sub> = 5 V, R <sub>L</sub> = 75 Ω |           | t <sub>r</sub>   | -    | 2    | -    | μs   |
| Fall time                 | V <sub>CC</sub> = 5 V, R <sub>L</sub> = 75 Ω |           | t <sub>f</sub>   | -    | 2    | -    | μs   |
| Turn-on time              | V <sub>CC</sub> = 5 V, R <sub>L</sub> = 75 Ω |           | t <sub>on</sub>  | -    | 3    | -    | μs   |
| Turn-off time             | V <sub>CC</sub> = 5 V, R <sub>L</sub> = 75 Ω |           | t <sub>off</sub> | -    | 2.3  | -    | μs   |
| Cut-off frequency         | V <sub>CC</sub> = 5 V                        |           | F <sub>CO</sub>  | -    | 250  | -    | kHz  |
| SATURATED                 |                                              |           |                  |      |      |      |      |
| Current                   |                                              | SFH610A-1 | I <sub>F</sub>   | -    | 20   | -    | mA   |
|                           |                                              | SFH6106-1 |                  |      |      |      |      |
|                           |                                              | SFH610A-2 | I <sub>F</sub>   | -    | 10   | -    | mA   |
|                           |                                              | SFH6106-2 |                  |      |      |      |      |
|                           |                                              | SFH610A-3 | I <sub>F</sub>   | -    | 10   | -    | mA   |
|                           |                                              | SFH6106-3 |                  |      |      |      |      |
|                           |                                              | SFH610A-4 | I <sub>F</sub>   | -    | 5    | -    | mA   |
|                           |                                              | SFH6106-4 |                  |      |      |      |      |
| SATURATED                 |                                              |           |                  |      |      |      |      |
| Rise time                 |                                              | SFH610A-1 | t <sub>r</sub>   | -    | 2    | -    | μs   |
|                           |                                              | SFH6106-1 |                  |      |      |      |      |
|                           |                                              | SFH610A-2 | t <sub>r</sub>   | -    | 3    | -    | μs   |
|                           |                                              | SFH6106-2 |                  |      |      |      |      |
|                           |                                              | SFH610A-3 | t <sub>r</sub>   | -    | 3    | -    | μs   |
|                           |                                              | SFH6106-3 |                  |      |      |      |      |
|                           |                                              | SFH610A-4 | t <sub>r</sub>   | -    | 4    | -    | μs   |
|                           |                                              | SFH6106-4 |                  |      |      |      |      |
| Fall time                 |                                              | SFH610A-1 | t <sub>f</sub>   | -    | 11   | -    | μs   |
|                           |                                              | SFH6106-1 |                  |      |      |      |      |
|                           |                                              | SFH610A-2 | t <sub>f</sub>   | -    | 14   | -    | μs   |
|                           |                                              | SFH6106-2 |                  |      |      |      |      |
|                           |                                              | SFH610A-3 | t <sub>f</sub>   | -    | 14   | -    | μs   |
|                           |                                              | SFH6106-3 |                  |      |      |      |      |
|                           |                                              | SFH610A-4 | t <sub>f</sub>   | -    | 15   | -    | μs   |
|                           |                                              | SFH6106-4 |                  |      |      |      |      |
| Turn-on time              |                                              | SFH610A-1 | t <sub>on</sub>  | -    | 3    | -    | μs   |
|                           |                                              | SFH6106-1 |                  |      |      |      |      |
|                           |                                              | SFH610A-2 | t <sub>on</sub>  | -    | 4.2  | -    | μs   |
|                           |                                              | SFH6106-2 |                  |      |      |      |      |
|                           |                                              | SFH610A-3 | t <sub>on</sub>  | -    | 4.2  | -    | μs   |
|                           |                                              | SFH6106-3 |                  |      |      |      |      |
|                           |                                              | SFH610A-4 | t <sub>on</sub>  | -    | 6    | -    | μs   |
|                           |                                              | SFH6106-4 |                  |      |      |      |      |
| Turn-off time             |                                              | SFH610A-1 | t <sub>off</sub> | -    | 18   | -    | μs   |
|                           |                                              | SFH6106-1 |                  |      |      |      |      |
|                           |                                              | SFH610A-2 | t <sub>off</sub> | -    | 23   | -    | μs   |
|                           |                                              | SFH6106-2 |                  |      |      |      |      |
|                           |                                              | SFH610A-3 | t <sub>off</sub> | -    | 23   | -    | μs   |
|                           |                                              | SFH6106-3 |                  |      |      |      |      |
|                           |                                              | SFH610A-4 | t <sub>off</sub> | -    | 25   | -    | μs   |
|                           |                                              | SFH6106-4 |                  |      |      |      |      |

**Note**

- All values presented are typical values

| SAFETY AND INSULATION RATINGS                |                                                                     |            |                |                    |
|----------------------------------------------|---------------------------------------------------------------------|------------|----------------|--------------------|
| PARAMETER                                    | TEST CONDITION                                                      | SYMBOL     | VALUE          | UNIT               |
| Climatic classification                      | According to IEC 68 part 1                                          |            | 55 / 100 / 21  |                    |
| Comparative tracking index                   | Insulation group IIIa                                               | CTI        | 175            |                    |
| Maximum rated withstanding isolation voltage | According to UL1577, t = 1 min                                      | $V_{ISO}$  | 4420           | $V_{RMS}$          |
| Tested withstanding isolation voltage        | According to UL1577, t = 1 s                                        | $V_{ISO}$  | 5300           | $V_{RMS}$          |
| Maximum transient isolation voltage          | According to DIN EN 60747-5-5                                       | $V_{IOTM}$ | 10 000         | V                  |
| Maximum repetitive peak isolation voltage    | According to DIN EN 60747-5-5                                       | $V_{IORM}$ | 890            | V                  |
| Isolation resistance                         | $V_{IO} = 500 \text{ V}$ , $T_{amb} = 25 \text{ }^{\circ}\text{C}$  | $R_{IO}$   | $\geq 10^{12}$ | $\Omega$           |
|                                              | $V_{IO} = 500 \text{ V}$ , $T_{amb} = 100 \text{ }^{\circ}\text{C}$ | $R_{IO}$   | $\geq 10^{11}$ | $\Omega$           |
| Output safety power                          |                                                                     | $P_{SO}$   | 400            | mW                 |
| Input safety current                         |                                                                     | $I_{SI}$   | 275            | mA                 |
| Input safety temperature                     |                                                                     | $T_{SI}$   | 175            | $^{\circ}\text{C}$ |
| Creepage distance                            | DIP-4 / SMD-4                                                       |            | $\geq 7$       | mm                 |
| Clearance distance                           |                                                                     |            | $\geq 7$       | mm                 |
| Creepage distance                            | DIP-4, 400 mil / SMD-4, 400 mil                                     |            | $\geq 8$       | mm                 |
| Clearance distance                           |                                                                     |            | $\geq 8$       | mm                 |
| Insulation thickness                         |                                                                     | DTI        | $\geq 0.4$     | mm                 |

**Note**

- As per IEC 60747-5-5, § 7.4.3.8.2, this optocoupler is suitable for “safe electrical insulation” only within the safety ratings. Compliance with the safety ratings shall be ensured by means of protective circuits.


**TYPICAL CHARACTERISTICS** ( $T_{amb} = 25 \text{ }^{\circ}\text{C}$ , unless otherwise specified)


Fig. 1 - Forward Voltage vs. Forward Current




Fig. 2 - Collector Current vs. Collector Emitter Voltage (NS)




Fig. 3 - Collector Current vs. Collector Emitter Voltage (saturated)




Fig. 6 - Normalized CTR (non-saturated) vs. Forward Current




Fig. 4 - Normalized Current Transfer Ratio (non-saturated) vs. Ambient Temperature




Fig. 7 - Normalized CTR (saturated) vs. Forward Current




Fig. 5 - Normalized Current Transfer Ratio (saturated) vs. Ambient Temperature




Fig. 8 - Phase Angle vs. Frequency




Fig. 9 - CTR Frequency vs. Collector Current




Fig. 10 - Switching Time vs. Load Resistance







Fig. 11 - Collector Emitter Voltage vs. Ambient Temperature (saturated)




## PACKAGE DIMENSIONS in inches (millimeters)





Pin 1 identification





i178027-1





### SMD



PIN 1 IDENTIFICATION




i178029-2









Option 6



Option 7




Option 8



18487

## PACKAGE MARKING (example of SFH610A-3X001)



### Notes

- XXXX = LMC (lot marking code)
- VDE logo is only marked on option 1 parts
- Tape and reel suffix (T) is not part of the package marking



## Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.