


technical standard:

技术标准:

1. Appearance: the surface of all parts shall be clean without rust, burr, crack or other mechanical damage
1. 外观: 各部件表面应清洁,不得有锈蚀、毛刺、裂纹或其他机械损伤。
2. Insulation endurance: each conductor shall be able to withstand Ac500V for 1 minute without current breakdo and arcing
2. 绝缘耐力: 各导体间应能受AC500V,1分钟的作用,而无电流击穿和飞弧现象
3. Insulation resistance: above DC 500 V, 100m Ω
3. 绝缘电阻:在 DC 500 V,100MΩ以上
4. Contact resistance value: the maximum contact resistance between conductors is 30m Ω
4. 接触抵抗值: 各导体间的接触电阻最大为30mΩ.
5. 5% salt spray for 24h without erythema, oxidation and other defects on the surface
5. 浓度5%盐雾24H表面而无红斑及氧化等不良。



广东星坤科技股份有限公司

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	PART NO.: PT-35373J148B
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED		WEIGHT
		SHEET 1/1
		REVISIC A0

