

2		1	
REV	CONTENT	CHK	DATE
V0.0	CONTENT	YL	22.11.16






Electrical :

- | | | |
|--|---|--------------------|
| | UL | IEC |
| 1.Rated Voltage : | 300V | 320V |
| 2.Rated Current : | 15A | 20A |
| 3.Torque Value : | M2.5 , 3.54Lb.in | M2.5 , 0.4N.m |
| 4.Wire Range: | 28-12AWG | 2.5mm ² |
| 5.Stripping Length : | 7-8mm | |
| 6.Withstanding Voltage : | AC1600V/1Min. | |
| 7.Operating Temperature : | -40°C~+105°C | |
| 8.RoHS Compliance | | |
| 9.Safety Approval : |  | |
| 10."★" is the key quality control point. | | |


2ETYKM - 5.08 - XXP - X X - 100

① ② ③ ④ ⑤ ⑥

- ① Series NO. ④ 1 Single Pitch
2 Double Pitch
- ② Pitch ⑤ Color: 1 Grey
2 Blue
3 Black
4 Green
5 Orange
6 Red
7 Transparent
8 Yellow
9 White
- ③ Poles
02 02Contacts
03 03Contacts
...
24 24Contacts
- ⑥ Customer Request: 100--Standard M2.5



SECTION A-A



6	SCREW-SIDE		XX	2	STEEL		Zn Plated	
5	SCREW		XX	N	STEEL		Zn Plated	
4	BLOCK		XX	N	BRASS		Ni Plated	
3	CLAMP		XX	N	PHOSPHOR BRONZE		Ni Plated	
2	COVER		XX	1	PA66 UL94V-0		SEE NOTE	
1	HOUSING		XX	1	PA66 UL94V-0		SEE NOTE	
ITEM	NAME OF PART		NO. OF PART	Q'TY	MATERIAL			NOTE
DWG.	YL	DATE	22.11.16	SIZE	A4	UNITS	mm	SHEET/OF 1 / 1
CHK.		DATE		SCALE	1:1			
APP.		DATE						
				NAME	2ETYKM-5.08-XXP-XX-100			
				DWGNO.	XXXX			



拓宜(上海)工控电器设备有限公司

Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.



拓宜(上海)工控电器设备有限公司
Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.

A	Total Pitch Tolerances in mm									Nominal dimension range in mm									$\perp$		$\equiv$	$-$		$//$	
	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10		over 0	over 100	over 150
	to 30	to 53	to 70	to 90	to 115	to 150	to 250	to 350	to 500	to 30	to 53	to 70	to 90	to 115	to 150	to 200	to 250	to 320	to 10		all	to 100	to 150		
	± 0.18	± 0.20	± 0.25	± 0.3	± 0.35	± 0.44	± 0.60	± 0.70	± 0.85	± 0.20	± 0.25	± 0.30	± 0.35	± 0.44	± 0.55	± 0.70	± 0.80	± 0.90	0.2	0.3	0.3	0.2	0.3	0.5	
	C									C												L			