






B向



A-A



### Material :

- (a) Housing : PA66(UL94V-0)
- (b) Screws : Steel , Cr<sup>3+</sup>Zn Plated
- (c) Cage : Brass , Ni Plated
- (d) Contact : Phosphor Bronze
- (e) Cover : PA66(UL94V-0)

### Electrical :

- 1.Rated Voltage : 300V
- 2.Rated Current : 8A
- 3.Torque Value : M2 , 1.77Lb.in
- 4.Wire Range: 28-16AWG
- 5.Stripping Length : 6-7mm
- 6.Withstanding Voltage : AC1600V/1Min.
- 7.Operating Temperature : -40℃~+105℃
- 8.RoHS Compliance
- 9.Safety Approval : cRus
- 10.Undimensioned Tolerances:

| Pitch Range In mm |        |         |       | Nominal Dimension Range In mm |          |           |       |         |
|-------------------|--------|---------|-------|-------------------------------|----------|-----------|-------|---------|
| ≤6                | 6 ~ 10 | 10 ~ 24 | ≥30   | 30 ~ 60                       | 60 ~ 100 | 100 ~ 150 | >150  | 0.05/10 |
| ±0.10             | ±0.15  | ±0.25   | ±0.20 | ±0.30                         | ±0.50    | ±0.70     | ±1.00 | ±0.1°   |

15ETYKAM - 3.5 - XXP - X X - 00

①

②

③

④

⑤

⑥

① Series No.

④ 1 Single Pitch  
2 Double Pitch

⑥ Customer Request :  
00--Standard

② Pitch

⑤ Color: 1 Grey  
2 Blue  
3 Black  
4 Green(Standard For AH)  
5 Orange  
6 Red  
7 Transparent  
8 Yellow  
9 White

③ Poles  
02 02Contacts  
03 03Contacts  
...  
24 24Contacts



拓宜(上海)工控电器设备有限公司

Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.

APPD: MA\_10/13/16'

CHKD: Yu\_10/12/16'

DRFT: Chen\_10/11/16'



THIRD ANGLE PROJECTION

PART NO.

15ETYKAM-3.5-XXP-XX-00

DRAWING NO.

REV

1

SHEET

1/1

MM  
(INCH)

DO NOT SCALE DRAWING

SCALE

1/1