






REV	CONTENT	CHK	DATE
V0.0	CONTENT	YL	22.11.16



SECTION A-A



Electrical :

- | | | |
|--|---------------|------------------------|
| | UL | IEC |
| 1.Rated Voltage : | 300V | 320V |
| 2.Rated Current : | 10A | 20A |
| 3.Wire Range: | 26-12AWG | 0.2-2.5mm ² |
| 4.Stripping Length : | 7-8mm | |
| 5.Withstanding Voltage : | AC1600V/1Min. | |
| 6.Operating Temperature : | -40°C~+105°C | |
| 7.RoHS Compliance | | |
| 8.Safety Approval : | cULus CE | |
| 9."★" is the key quality control point | | |

2ETYKD - 5.08 -XXP - X X - 00

① ② ③ ④ ⑤ ⑥

① Series NO. ④ 1 Single Pitch
2 Double Pitch

② Pitch:5.08mm ⑤ Color: 1 Grey
2 Blue
3 Black
4 Green
5 Orange
6 Red
7 Transparent
8 Yellow
9 White

⑥ Customer Request: 00--Standard

5	SPRING	XX	N	Stainless Steel	--
4	CLAMP	XX	N	Phosphor Bornze	Ni Plated
3	BUTTON	XX	N	POM UL94HB	SEE NOTE
2	COVER	XX	1	PA66 UL94V-0	SEE NOTE
1	HOUSING	XX	1	PA66 UL94V-0	SEE NOTE
ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTE
DWG.	YL	DATE	22.11.16	SIZE	A4 UNITS mm SHEET/OF 1 / 1
CHK.	DATE			SCALE	1:1
APP.	DATE				
				NAME	2ETYKD-5.08-XXP-XX-00
				DWGNO.	XXXX



拓宜(上海)工控电器设备有限公司
Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.

A	Total Pitch Tolerances in mm									Nominal dimension range in mm								$\perp$		$\equiv$	$-$		$//$	
	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 0	over 10	all	over 0	over 100	over 150
	to 30	to 53	to 70	to 90	to 115	to 150	to 250	to 350	to 500	to 30	to 53	to 70	to 90	to 115	to 150	to 200	to 250	to 320	to 10	to 100		to 150		
	± 0.18	± 0.20	± 0.25	± 0.3	± 0.35	± 0.44	± 0.60	± 0.70	± 0.85	± 0.20	± 0.25	± 0.30	± 0.35	± 0.44	± 0.55	± 0.70	± 0.80	± 0.90	0.2	0.3		0.3	0.2	0.3