

MESSRS.

SPECIFICATION FOR APPROVAL**承 认 书**

Product	DYNAMIC SPEAKER
Part No.	HDK-302008ZA-5C6 (RoHS)
Customer	
Customer Part No.	

Approved By	Checked By	Made By
王台平 MAR-29-2019	曹丽萍 MAR-29-2019	LILY MAR-29-2019

常州华龙电子有限公司**DRAGONSTATE ELECTRONIC CORPORATION**

中国江苏省常州市新区电子园新四路 36 号

Tel: +86-519-85110078. 86-519-85106698, Fax: +86-519-85101081

EDITION:1.4

1.Specification
HDK-302008ZA-5C6(RoHS)

ITEM		SPECIFICATIONS	
01	Type	Dynamic speaker	
02	Dimension	External diameter 30 × 20 mm	
03	Rated Input Power	1.5W	
04	Max. Input Power	1.8W for 1 minute	
05	Impedance	8 ohm ± 15% at 2000Hz.	
06	Resonance Frequency (Fo)	1000Hz ± 20% at Fo, 1V	
07	Sensitivity (S.P.L.)	98dB(0.5W/0.1m) ± 3 dB	at AVE 1.0 ,1.2 ,1.5,2.0 KHz.
08	Frequency Range	Fo – 20KHz	
09	Total Harmonics Distortion	Max 8 % at 1 KHz,1.5W.	
10	Voice Coil	Diameter 13.3mm	
11	Magnet	Rare earth permanent (Nd-Fe-B) magnet 12.5*2.2 mm	
12	Weight	8.5g ± 1.0g	
13	Appearance	Should not exist any obstacle to be harmful to normal operation; damages, cracks, rusts and distortions, etc.	
14	Operation Test	Must be normal at program source – 1.5W	
15	Buzz, Rattle, etc.	Should not be audible at 3.46V sine Wave between Fo to 20KHz	
16	Polarity	When positive voltage is applied to the terminal marked (+), diaphragm should move to the front.	
17	Terminal Strength	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.	
18	Temperature	Operating temperature: -20°C to +60°C Storage temperature: -30°C to +70°C	

2-1. Test Condition

STANDARD

Temperature : 15 ~ 35°C

Relative humidity : 25% ~ 85%,

Atmospheric pressure : 860mbar to 1060mbar.

BASIC

Temperature : 20±3°C

Relative humidity : 60% ~ 70%,

Atmospheric pressure : 860mbar to 1060mbar

2-2. Standard Test Fixture


1. Input Power : 0.5W (2.0V)

2. Zero Level : -dB


3. Mode : SPEAKER

4. potentiometer Range : 50dB

5. Sweep Time : 0.5sec




2-3. Frequency Response Curve




Mode: SPEAKER



3.Dimension



4. Reliability Tests





Items.		Specifications
01	High temp. Test	Keep 96 hours at $+70^{\circ}\text{C}\pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
02	Low temp. Test	Keep 96 hours at $-30^{\circ}\text{C}\pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
03	Humidity test	Keep 96 hours at $+40^{\circ}\text{C}\pm 3^{\circ}\text{C}$ relative humidity 95% and leave 3 hours in normal temperature and then checked.
04	Temp./Humidity cycle	<p>The part shall be subjected 5 cycles. One cycle shall be 12 hours and consist of;</p> 
05	Thermal cycle test.	Low temperature: $-30^{\circ}\text{C}\pm 3^{\circ}\text{C}$, temperature: $+70^{\circ}\text{C}\pm 3^{\circ}\text{C}$, cycle: 1 hour/cycle each, and then keep 5 cycles in a room.
06	Vibration	10~200~10Hz sin-wave sweep 15min. 5G(constant) X,Y, Z 3 direction. 2 hours each, total 6 hours.
07	Fix drop test	Fix on jig. Then drop from 152cm height to the concrete floor X, y, z 6 direction. 5 times each, total 30 times.
08	Free drop test	Free drop from 100cm height to the concrete floor X, y, z 6 direction. 1 times each, total 6 times.
09	Rated Power test	Rated Power white noise is applied for 96 hours
10	Max Power test	Max power 1 min on – 2 min off 10 cycles.
11	Terminal strength test	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.
<p>Criterion: After these test , the change of S.P.L shall be within ± 3 dB .</p>		

Soldering Condition

Recommend using constant branding iron in **15 ~ 30W**, and in temperature range **$350\pm 10^{\circ}\text{C}$** .

Soldering time not over **3** seconds.

5.Packing

REV NO.	REVISION NOTE	APPROVAL	DATE
	 <p>Cover(350*285*5mm) Material: Paper</p>		
	 <p>Box(350*285*20mm) 50pcs Material: Paper+Epe</p>		
	 <p>Middle(320*220*120mm) 450pcs(9*50pcs) Material: Paper+Epe</p>		
	 <p>Outer Box(590*390*405mm) 1800pcs(4*450pcs) Material: Paper</p>		
单位: mm			
TITLE: packing		DRAWN: Lily	2016/08/15
PART NO.		DESIGNED: R&D OF D.S.	SCALE: 2:1
DWG NO.		CHECKED: Emily	SHEET: 1 of 1
1 REV		APPROVAL: Eric	UNITS: mm
		MATERIAL: ***	TOLERANCE
			20~11 ± 0.3
			10~5 ± 0.2
			<4 ± 0.1
<div style="border: 1px solid black; display: inline-block; padding: 2px 5px;">DS</div> DRAGONSTATE ELECTRONIC CORPORATION			

