








Technical Index:

1. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. Rated voltage: 200V DC/AC(rms).
3. Rated current: 2.0A.
4. Contact resistance: $\leq 25\text{m}\Omega$.
5. Withstanding voltage: 500V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.



SECTION A-A



Part No	Pin	A	B
XY-HY2.0-2A11-YT	2	2.00	6.00
XY-HY2.0-3A11-YT	3	4.00	8.00
XY-HY2.0-4A11-YT	4	6.00	10.00
XY-HY2.0-5A11-YT	5	8.00	12.00
XY-HY2.0-6A11-YT	6	10.00	14.00
XY-HY2.0-7A11-YT	7	12.00	16.00
XY-HY2.0-8A11-YT	8	14.00	18.00
XY-HY2.0-9A11-YT	9	16.00	20.00
XY-HY2.0-10A11-YT	10	18.00	22.00
XY-HY2.0-11A11-YT	11	20.00	24.00
XY-HY2.0-12A11-YT	12	22.00	26.00
XY-HY2.0-13A11-YT	13	24.00	28.00
XY-HY2.0-14A11-YT	14	26.00	30.00
XY-HY2.0-15A11-YT	15	28.00	32.00
XY-HY2.0-16A11-YT	16	30.00	34.00
XY-HY2.0-17A11-YT	17	32.00	36.00
XY-HY2.0-18A11-YT	18	34.00	38.00
XY-HY2.0-19A11-YT	19	36.00	40.00
XY-HY2.0-20A11-YT	20	38.00	42.00

序号	品名	材质
1	基座Wafer	PA66 UL94V-2 黄色
2	端子Contact	铜合金/镀锡

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: WAFER 2.0 180° DIP 黄色 带扣	
.X±0.35	.X*±5°	CHK.	Jack	DWG NO. XY-HY2.0-NA11-YT	
.XX±0.25	.X*±3°	DRA.	Can	PROJ. CUSTOMER DRAWING	
.XXX±0.15	.XX*±1°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A