

Technical Index:

- 1.The surface of the plastic parts should be smooth,no rough edges,no obvious shrinkage,defects,cracks and other phenomena)
- 2.Lock Configuration: 2 to 3Pin is 1.≥4Pin is 2
- 3.Temperature range: -25°C~+85°C.
- 4.Rated voltage: 125V.AC/DC.
- 5.Contact resistance: ≤0.02Ω.
- 6.Insulation resistance: ≥100MΩ

Part No	Pin	A	B	C
XY-MX1.25-2A11-R	2	1.25	3.20	4.30
XY-MX1.25-3A11-R	3	2.50	4.45	5.55
XY-MX1.25-4A11-R	4	3.75	5.70	6.80
XY-MX1.25-5A11-R	5	5.00	6.95	8.05
XY-MX1.25-6A11-R	6	6.25	8.20	9.30
XY-MX1.25-7A11-R	7	7.50	9.45	10.55
XY-MX1.25-8A11-R	8	8.75	10.70	11.80
XY-MX1.25-9A11-R	9	10.00	11.95	13.05
XY-MX1.25-10A11-R	10	11.25	13.20	14.30
XY-MX1.25-11A11-R	11	12.50	14.45	15.55
XY-MX1.25-12A11-R	12	13.75	15.70	16.80
XY-MX1.25-13A11-R	13	15.00	16.95	18.05
XY-MX1.25-14A11-R	14	16.25	18.20	19.30
XY-MX1.25-15A11-R	15	17.50	19.45	20.55
XY-MX1.25-16A11-R	16	18.75	20.70	21.80
XY-MX1.25-17A11-R	17	20.00	21.95	23.05
XY-MX1.25-18A11-R	18	21.25	23.20	24.30
XY-MX1.25-19A11-R	19	22.50	24.45	25.55
XY-MX1.25-20A11-R	20	23.75	25.70	26.80

SECTION A-A

序号	品名	材质
1	基座Wafer	PA66 红色
2	端子Contact	铜合金/镀锡

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	Alex	TITLE: WAFER 1.25 180° DIP 红色	
.X±0.35	.X*±5°	CHK.	Jack	DWG NO. XY-MX1.25-NA11-R	
.XX±0.25	.X*±3°	DRA.	Can	PROJ. CUSTOMER DRAWING	
.XXX±0.15	.XX*±1°	SIZE	A4	SCALE	1:1
		SHEET	1/1	REV.	A