

Specification Sheet

Part Number: 155-17801



Clip includes an internal rib that spans the inside of the bracket to fit securely into the profile of the tubing to prevent lateral movement and slipping of the tubing.

Extended fir tree allows for a wide range of panel thicknesses.

Fir tree design provides low insertion forces and high extraction forces.

Convoluted Tubing Clip, 0.4" Max Bundle Diameter, 0.02 - 0.12" Panel Thick, PA66HIRHS, Black, 500/pkg

Article Number 155-17801

Type CTC10FT9

Color Black (BK)

Quantity Per bag

Product Description

Convoluted Tube Clips provide a quick and easy method for firmly securing corrugated covered cables and wires to a surface. Applications such as this can be found in a wide variety of industries such as the wire harness, automotive, trucking, and heavy equipment manufacturing industries.

Short Description

Convoluted Tubing Clip, 0.4" Max Bundle Diameter, 0.02 - 0.12" Panel Thick, PA66HIRHS, Black, 500/pkg

Global Part Name CTC10FT9-PA66HIRHS-BK

Fixation Method Fir Tree

Variant Clips

Width W (Imperial) 0.31

Width W (Metric) 8.0

Height H (Imperial) 0.89

Height H (Metric) 22.7

Nominal Diameter (Imperial) 0.38

Nominal Diameter (Metric) 10.0

Panel Thickness Min (Imperial) 0.12

Panel Thickness Max (Imperial) 0.20

Panel Thickness Min (Metric) 3.0

Panel Thickness Max (Metric) 5.0

Mounting Hole Diameter D (Imperial) 0.34 - 0.35

Mounting Hole Diameter D (Metric) 8.7 - 9.0 mm

Mounting Hole Diameter D Min (Imperial) 0.34

Mounting Hole Diameter D Max (Imperial) 0.35

Mounting Hole Diameter D Max (Metric)	9.0
Disc Diameter (Metric)	23.0
Disc Diameter (Imperial)	0.87
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Flammability	UL 94 HB
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)