

■ Features

- Molding Inductor.
- Low Profile,Low Temp.
- Large Current(Over 15A).
- Customize For Different Need.
- Operating temperature:-40℃ ~ +125℃.

■ Applications

- General Electronic.
- Video Device,TV,TFT.
- Power Module for PC.
- NB/Lap Top Computer.
- Server,VGA Card/Module.

■ Product Identification

YSPI □□□□□ — □□□ □
 (1) (2) (3) (4)


(1) : Type

(2) : Dimensions

(3) : Inductance value

(4) : Inductance Tolerance: N=±30%,M=±20%

■ Shapes and Dimensions (Unit: mm)



TYPE	A	B	C Max.	D	E	G Ref.	H Ref.	I Ref.
YSPI1050Y	10.5±1.0	10.3±0.3	5.0	2.8±0.3 Flatten OR 3.0±0.3	2.0±0.5	6.0	4.0	3.5

■ YSPI1050Y Series


Part Number	Inductance (μ H) @100KHz	DC Resistance (m Ω)		Heat Rating Current (A)	Saturation Current (A)
		Typ.	Max.		
YSPI1050Y-R36M	0.36	0.8	1.05	36.0	52.0
YSPI1050Y-R68M	0.68	1.6	1.9	20.0	35.0
YSPI1050Y-R82M	0.82	2.1	2.5	18.0	30.0
YSPI1050Y-1R0M	1.0	2.1	2.5	16.0	28.0
YSPI1050Y-1R2M	1.2	2.3	2.8	15.0	25.0
YSPI1050Y-1R5M	1.5	3.2	3.8	13.0	22.0
YSPI1050Y-2R2M	2.2	5.0	6.0	11.0	20.0
YSPI1050Y-3R3M	3.3	5.8	7.0	10.0	15.0
YSPI1050Y-4R7M	4.7	9.7	12.0	9.0	15.0
YSPI1050Y-5R6M	5.6	13.5	16.0	8.5	14.0
YSPI1050Y-6R8M	6.8	14.5	17.0	8.0	13.0
YSPI1050Y-8R2M	8.2	23.0	27.0	7.0	12.0
YSPI1050Y-100M	10	24.5	28.0	6.5	11.0
YSPI1050Y-150M	15	37.0	42.0	6.0	10.0
YSPI1050Y-220M	22	58.0	65.0	5.0	8.0
YSPI1050Y-330M	33	85.0	95.0	4.5	6.0
YSPI1050Y-470M	47	136.0	152.0	4.0	5.5
YSPI1050Y-680M	68	198.0	215.0	3.0	5.0
YSPI1050Y-820M	82	220.0	240.0	2.5	4.5
YSPI1050Y-101M	100	230.0	250.0	2.2	4.0
YSPI1050Y-151M	150	394.0	435.0	2.0	3.5
YSPI1050Y-181M	180	420.0	460.0	1.8	2.8
YSPI1050Y-201M	200	435.0	470.0	1.5	2.5

※ The saturation current value is the DC current value having inductance decrease down to 30%. (at 20℃)

※ The temperature rise current value is the DC current value having temperature increase up to 40℃. (at 20℃)


※ The rated current is the DC current value that satisfies both of current value saturation current value and temperature rise current value.

■ Taping Dimensions(Unit:mm)




TYPE	W	A	B	C	D	E	P	K Ref	T	MPQ
YSPI1050Y	24 ± 0.3	10.6 ± 0.1	11.3 ± 0.1	10.75	11.5 ± 0.1	4.4 ± 0.1	16 ± 0.1	4.6	0.40 ± 0.05	800

■ Reel Dimensions(Unit:mm)




TYPE	W	W1	W2	W3	A	B	C	D
YSPI1050Y	330 ± 2.0	24.4 ± 1.5	30.4MAX	23.9 Min	13.0 ± 0.50	21.0 ± 0.80	2.0 ± 0.50	100 Min

■ Direction of rolling



■ Cover tape peel off condition



Cover tape peel force shall be 0.1N to 1.3N.

Reference peel speed 300±10mm/min.