




技术特性/Specifications:

额定电压 Rated voltage: 125V AC, DC

额定电流 Rated current: 1A AC, DC


接触电阻 Contact resistance: 20m Ω max

绝缘电阻 Insulation resistance: 100M Ω min

耐压 Withstand voltage: 250V AC/minute

环境温度 Ambient temperature: -40 $^{\circ}$ C $\sim$ +105 $^{\circ}$ C

适用线规 Wire range: AWG#32 $\sim$ #28



REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Available in 02 through 15 Circuits.
Material : Nylon UL94V-0(2).
Accepts DL12507-T Crimp Terminal.



Circuits	Type	Dimension mm		Circuits	Type	Dimension mm	
		A	B			A	B
2	SGN-2Y	1.25	3.00.	9	SGN-9Y	10.00	11.75
3	SGN-3Y	2.50	4.25	10	SGN-10Y	11.25	13.00
4	SGN-4Y	3.75	5.50	11	SGN-11Y	12.50	14.25
5	SGN-5Y	5.00	6.75	12	SGN-12Y	13.75	15.50
6	SGN-6Y	6.25	8.00	13	SGN-13Y	15.00	16.75
7	SGN-7Y	7.50	9.25	14	SGN-14Y	16.25	18.00
8	SGN-8Y	8.75	10.50	15	SGN-15Y	17.50	19.25

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO.,LTD			
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:		TITLE:	
.XX: ± 0.15	.X° : ± 2.0°	DL12507 (SGN)-Y		1.25 mm Pitch Housing	
.XXX: ± 0.01	.XX° : ± 1.0°	DR:Chen Quan Long	DATE:21/06/07	PART NO:	
FINISH:		CHKD: Wu Hui	DATE:21/06/07	SCALE: N/A	PAGE: 1/1
DRAWING NO:		APPD: Ren An De	DATE:21/06/07	UNITS: mm	REV. : A


REV.	REVISION DESCRIPTION	DATE	APPD

NOTES

Used in DL12507-Y Series Housing.
Accepts AWG #28~32 Wire Range.
0.08~ 0.032 mm² .
Insulation O.D.=0.7~1.0 mm.
Material : Phosphor Bronze .
Finish: Tin plated.
Thickness: 0.15 mm.



SECTION A-A



SECTION B-B

GENERAL TOLERANCES (UNLESS SPECIFIED)		ZHE JIANG DELI CONNECTORS CO., LTD	
.X: ± 0.25	X° : ± 3.0°	PRODUCT NAME:	TITLE:
.XX: ± 0.15	.X° : ± 2.0°	DL12507 (SGN)-T	1.25 mm Pitch Crimp Terminal
.XXX: ± 0.01	.XX° : ± 1.0°	DR: Chen Quan Long	DATE: 21/08/01
FINISH:		CHKD: Wu Hui	DATE: 21/08/01
DRAWING NO:		APPD: Ren An De	DATE: 21/08/01
		SCALE: N/A	PAGE: 1/1
		UNITS: mm	REV.: A