

Specifications

Coupling : Threaded coupling

Shell material: Zinc alloy with Nickel Plate

Insert material: bakelite

Contact material: copper Silver Plate/Nickel

Termination: Solder

Mating cycle: 500


Cable diameter: -20°C +85°C

Ordering Information

XD - GX12 - NP - *

No. of Pin
2-7 Pin

Contact
Type
F=Female
M=Male



NO. of contacts	芯数	2	3	4	5	6	7
Rated current (A)	额定电流	5A	5A	5A	5A	5A	5A
Operation limit voltage(AC.V.rms)	工作电压(AC.V)分钟	200V	125V	125V	125V	125V	125V
Withstanding voltage(AC.V.rms) 1 minute	耐压	1500	1500	1500	1500	1500	1500
Insulation resistance (mΩ)	绝缘阻抗	2000	2000	2000	2000	2000	2000
Contact resistance (mΩ)	接触阻抗	5	5	5	5	5	5
Solder cup mouth aperture	焊杯口径φ(mm)	φ0.8	φ0.8	φ0.8	φ0.8	φ0.8	φ0.8
Solder inter diameter	接触体孔径φ(mm)	φ1.2	φ1.2	φ1.2	φ1.2	φ1.2	φ1.2

			GENERAL TOLERANCE	制图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	GX12 航空插头 母头	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	XD-GX12-NP-F	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
1	初版发行		Angle ±3.0°					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						