

承 認 書
PRODUCT APPROVAL SHEET

产品名称 PRODUCT Name : 轻触开关

规格型号 PART NO : 6*6 中二脚脚长 3.5(3.2 座)

物 料 号 PART NO :

制表/DESIGNED BY	校对/CHECKED BY	审核/APPROVED BY	
吴永余	吴永友	张 鹏	
DATE 日期 20201117	DATE 日期 20201117	DATE 日期 20201117	

贵司承认栏 APPROVAL SIGNATURE
贵司名称/CUSTOMER NAME:

贵司物料名称/CUSTOMER TYPE:


贵司物料号/CUSTOMER NO:


请于 年 月 日前承认返 日期 DATE:
PLEASE RETURN TO US AFTER CONFIRMED! THANK YOU!



ISSUE	DATE	WRTN	CHKD	Page 1 of 7
001	2020. 11. 17	WU	ZHANG	

深圳市金航标电子有限公司			产品系列	轻触开关
TACT SWITCH SPECIFICATION 轻触开关产品承认书				
1、概述 GENERAL 1.1 适用范围 APPLICATION 此规格书适用于机械式轻触开关的相关要求 This specification is applied to the requirements for TACTILE SWITCH(MECHANICAL CONTACT) 1.2 工作温度范围 Operating Temperature Range -20℃~70℃ (在标准大气压、标准温度条件下) -20℃~70℃ (Normal humidity, normal air pressure) 1.3 贮藏温度范围 Storage Temperature Rane -40℃~85℃ (在标准大气压、标准温度条件下) -40℃~85℃ (Normal humidity, normal air pressure) 1.4 测试条件 Test Conditions 在没有其它特定的条件下，应该在以下的条件下进行测试和测量： Unless otherwise specified, tests and measurement shall be made in the following standard conditions 常温.....5℃~35℃ Normal temperature.....5℃~35℃ 标准湿度.....相对湿度 45%~85% Normal humidity.....relative humidity 45%~85% 标准大气压.....86KPa~106 KPa Normal air pressure.....86KPa~106 KPa 在制造过程中，测试和测量应该在以下的条件下进行： If any doubt arise from the judgment, tests shall be conducted at the following conditions 温度.....20℃±2℃ Temperature.....20℃±2℃ 相对湿度.....65%±5% Relative humidity.....65%±5% 环境气压.....86KPa~106 KPa Air pressure.....86KPa~106 KPa 2、详细说明 Detailed specification 2.1 外观：应无影响、降低产品性能的缺陷 Appearance:There should be no defects that affect the serviceability of product. 2.2 结构尺寸和安装尺寸：应符合装配图要求 Style and dimension:shall conform to the assemble drawings.				
ISSUE	DATE	WRTN	CHKD	Page 2 of 7
001	2020.11.17	WU	ZHANG	

深圳市金航标电子有限公司			产品系列	轻触开关
TACT SWITCH SPECIFICATION 轻触开关产品承认书				
2.3 操作形式：有触觉反应的操作 Type of actuating:Tactile feedback. 2.4 开关结构：单回路输出（具体的触点结构在装配图中已绘出） Contact arrangement:1 pole,1 throw (Details of contact arrangement are given in the assembly drawings.) 2.5 开关工作额定值：DC12V 50mA Ratings: DC12V 50mA				
测试项目 TEST ITEM				
3. 电器性能 ELECTRICAL PERFORMANCE				
3-1 接触电阻 CONTACT RESISTANCE 在 1kHz 小电流电压（50mA，20mV）下测量。 Being tested at 1kHz small current and voltage (50mA，20mV) by contact resistance meter. 100 毫欧以下。 100mΩ max.				
3-2 绝缘电阻 INSULATION RESISTANCE 在端子之间和端子与壳之间加 DC250V 条件下，持续 1 分钟测量。 DC 250v shall be applied for test between terminals and between terminals and frame for one minute. 100 兆欧以上。 100MΩ min.				
3-3 耐电压 WITHSTAND VOLTAGE 在端子之间和端子于壳之间加 AC250V（50Hz 或 60Hz）感应电流 1mA 条件下，持续 1 分钟测量。 AC 250V and induction current 1mA shall be applied for test between terminals and between terminals and frame for one minute. 无击穿现象。 There shall be no breakdown.				
4. 机械性能 MECHANICAL PERFORMANCE				
4-1 动作力 OPERATING FORCE 160±30gf 260±50gf				
ISSUE	DATE	WRTN	CHKD	Page 3 of 7
001	2020.11.17	WU	ZHANG	

深圳市金航标电子有限公司				产品系列	轻触开关
TACT SWITCH SPECIFICATION 轻触开关产品承认书					
5. 耐久性 DURABILITY					
5-1 可焊性试验 SOLDERING TEST					
端子顶部被侵入锡池 0.5mm 深，温度 $260\pm5^{\circ}\text{C}$，时间 5秒。 The tip of the terminal shall be dipped 0.5mm in the solder bath within temperature of $260\pm5^{\circ}\text{C}$ for 5s. 侵入的部分 95%以上表面将被锡覆盖 Over 95% of the immersed surface was covered by tin .					
5-2 耐焊性试验 SOLDERING RESISTANT TEST					
焊炉锡的温度控制在 $260\pm5^{\circ}\text{C}$，时间为 3 ± 0.5 秒, 与(基板)厚度 1.6mm. Soldering temperature $260\pm5^{\circ}\text{C}$, soldering time $3\pm0.5\text{s}$, immersion depth up to the surface of the board, thickness of PCB 1.6mm. 手焊接时温度控制在 $350\pm5^{\circ}\text{C}$，时间为 3 ± 0.5 秒，但不能在端子上施加异常压力。 Manual soldering temperature $350\pm5^{\circ}\text{C}$, soldering time $3\pm0.5\text{s}$, however excessive pressure shall not be applied to the terminal. 本体无变形, 能满足与机械、电器性能。 Without deformation of case or excessive looseness of electrical properties					
5-3 波峰焊接热试验 WAVE SOLDERING HEAR TEST					
本体无变形, 能满足与机械、电器性能。 Without deformation of case or excessive looseness of electrical properties					
 Time inside soldering equipment Temperature Profile					
ISSUE	DATE	WRTN	CHKD	Page 5 of 7	
001	2020. 11. 17	WU	ZHANG		

深圳市金航标电子有限公司

产品系列

轻触开关

TACT SWITCH SPECIFICATION
轻触开关产品承认书

5-4 寿命测试 LIFE TEST

无负载条件, 每分钟 100-120 次的速度操作 100, 000 次。

100, 000cycles of operation at a rate of 100-120 cycles per minute with unloading

(1) 接触电阻 200 毫欧以下。Contact resistance 200mΩ

(2) 动作力变化范围初始值 30%。Operating force 30% initial value.

(3) ITEM 项目——1.2

(4) ITEM 项目——1.3

(5) ITEM 项目——2.2

5-5 盐雾 SAIL SPRA

1) 测试温度: 35±2℃ Temperature: 35±2℃

2) 循环次数: 4小时喷雾 1 小时停, 连续 1 次。喷雾 4 小时。Cycle: 4 Hours testing (1 Times) and 1 Hours stop. Based on total 4 hours.

3) 盐雾浓度: 5±1% Salt solution concentration: 5±1% by weight.

(1) 接触电阻 200 毫欧以下。Contact resistance 200mΩ.

(2) 绝缘电阻 100 兆欧以上。Insulation resistance 100MΩ min.

(3) 无任何迹象显示机械及电器性能之损坏

there shall be no sign of mechanical and electrical damage.

5-6 耐热试验 HEAT RESISTANT TEST

在 80±2℃ 环境中放 96 小时, 再置于正常环境中, 30 分钟后进行测试。
80±2℃ for 96H, test after keeping in normal condition for 30min.

5-7 耐湿试验 MOISTURE RESISTANT TEST

在 60±2℃ 90~95% 环境中放 96 小时, 再置于正常环境中, 30 分钟后进行测试。

At 60±2℃ 90~95% RH for 96H, test after keeping in normal condition for 30min.


5-8 耐冷试验 COLD RESISTANT TEST

在 -40±2℃ 环境中放 96 小时, 再置于正常环境中, 30 分钟后进行测试。
At -40±2℃ for 96H, test after keeping in normal condition for 30min.

5-9 温度交变试验 TEMPERATURE CYCLIG TEST

如图示之环境中, 循环 5 次后, 再置于正常环境中, 1 个小时后进行测试。

According to following figure, after 5 cycles, test after keeping in normal condition for 1H.



(1) 接触电阻 200 毫欧以下。

Contact resistance 200mΩ.

(2) 绝缘电阻 100 兆欧以上。

insulation resistance 100MΩ min.

(3) 无任何迹象显示机械及电器性能之损坏

there shall be no sign of mechanical and electrical damage.

ISSUE

DATE

WRTN

CHKD

001

2020. 11. 17


WU

ZHANG




Page 6 of 7

Kinghelm®



D	H	
3.5	4.3	
	4.5	
	5.0	
3.3	5.5	
	6.0	
	6.5	
	7.0	
	7.3	
3.0	7.5	
	8.0	
	8.5	
	9.0	
	9.5	
	10.0	



T=0.3




P C B 参考图



技术参数

1. 额定电流:50mA 12V DC
2. 接触电阻:100毫欧
3. 行程:0.3±0.1mm
4. 绝缘电阻:100兆欧
5. 耐电压:250v 50Hz 1Min



电器原理图

按力	160±30gf	260±50gf
----	----------	----------

寿命	10万次	10万次
----	------	------

										第一视角		比例	规格型号/ Part No	6*6中二脚脚长3.5(3.2座)
E	盖板	铁0.25	1	镀铜锡						一般公差		1:1	物料号/ Part No	KH-6X6X7.5H-Z2J
D	按钮	PPA	1	清洗						>0.5-2	±0.1	单位		
C	簧片	不锈钢覆银	1		標記	處數	更改文件號	簽字	日期	>2-5	±0.2			
B	基座	PPA	1	清洗						>5以上	±0.3			
A	卡件	黄铜0.30	1	镀银						角度	±1°			
序号	名称	材 料	数量	备 注	设计/Designed		审核/Checked		批准/Approved		深圳市金航标电子有限公司			
					吴永余		张 鹏		何春林		www.kinghelm.com.cn		0755-28190160	

深圳市金航标电子有限公司

www.kinghelm.com.cn

0755-28190160