

Specification Sheet

Part Number: 151-03103



Mount and tie combination makes it easy to service bundles in the field. Eliminates the need for multiple sized diameter clamps.

Low fire hazard materials comply with stringent NFPA 130 safety standards and improve opportunities to get product specified at the engineering stage of a project.

High Torque Mount, Mounting Hole Dia. 0.327", Max Torque 114.0 lb - ft, PA666V0, Black, 500/pkg

Article Number	151-03103
----------------	-----------

Type	HDM320
------	--------

Color	Black (BK)
-------	------------

Quantity Per	carton
--------------	--------

Product Description	The saddle design minimizes pinching and crushing of wires and adjusts to a wide variety of bundle diameters when used with HellermannTyton heavy duty T120, T150 or Wide Strap Cable Ties. Metal bushing provides strength for high-torque applications. Low fire hazard material is designed specifically for rail applications.
---------------------	--

Short Description	High Torque Mount, Mounting Hole Dia. 0.327", Max Torque 114.0 lb - ft, PA666V0, Black, 500/pkg
-------------------	---

Global Part Name	HDM320-PA666V0-BK
------------------	-------------------

Length L (Imperial)	1.82
Length L (Metric)	46.5
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.98
Width W (Metric)	25.0
Height H (Imperial)	0.81
Height H (Metric)	20.7
Cable Tie Width Max (Imperial)	0.5
Cable Tie Width Max (Metric)	12.7
Mounting Hole Diameter D (Imperial)	0.33
Mounting Hole Diameter D (Metric)	8.31 mm
Stud Diameter (Metric)	8.0 mm
Stud Diameter (Imperial)	0.31
Material	Polyamide 6.6/6, V0 (PA666V0)
Material Shortcut	PA666V0

Flammability	UL 94 V-0
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +248°F (-40°C to +120°C)
Maximum Torque (kgf-cm)	1576.11
Maximum Torque (lbf-ft)	114
Reach Compliant (Article 33)	No
ROHS Compliant	Yes
Certification/Specification	Exova NFPA130: 2017 ASTM 1354 ASTM E 162 ASTM E 662
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)