


REV	CONTENT	CHK	DATE
V0.0	CONTENT	YL	22.11.17

Electrical :

1. Rated Voltage : **UL** 300V **IEC** 320V
 2. Rated Current : 15A 20A
 3. Withstanding Voltage : AC1600V/1Min.
 4. Operating Temperature : -40°C~+105°C
 5. RoHS Compliance
 6. Safty Approval : 
 7. "★" is the key quality control point.

2ETYV - 5.0 -XXP - 1 4 - 100
 ① ② ③ ④ ⑤ ⑥

- ① Sereies NO. ④ 1 Single Pitch
 2 Double Pitch
 ② Pitch ⑤ Color: 1 Grey
 2 Blue
 3 Black
 4 Green
 5 Orange
 6 Red
 7 Transparent
 8 Yellow
 9 White
 ⑥ Customer Request: 100--Standard




SECTION A-A




★ 3.80±0.3

★ 8.60±0.2

2	PIN	XX	P	BRASS	Tin Plated
1	HOUSING	XX	1	PA66 UL94V-0	SEE NOTE
ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL	NOTE
DWG.	YL	DATE	22.11.17	SIZE	A4 UNITS mm SHEET/OF 1 / 1
CHK.	DATE		SCALE	1:1	
APP.	DATE				
 拓宜(上海)工控电器设备有限公司 Topone(Shanghai) Industrial Control Electrical Equipment Co., LTD.				NAME	2ETYV-5.0-XXP-14-100
				DWGNO.	XXXX



PCB Layout



A	Total Pitch Tolerances in mm									Nominal dimension range in mm									$\perp$		$\equiv$	$-$	$//$						
	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 0	over 10	all	over 0	over 100	over 150					
	to 30	to 53	to 70	to 90	to 115	to 150	to 250	to 350	to 500	to 30	to 53	to 70	to 90	to 115	to 150	to 200	to 250	to 320	to 10			to 100	to 150						
	± 0.18	± 0.20	± 0.25	± 0.3	± 0.35	± 0.44	± 0.60	± 0.70	± 0.85	± 0.20	± 0.25	± 0.30	± 0.35	± 0.44	± 0.55	± 0.70	± 0.80	± 0.90	0.2	0.3	0.3	0.2	0.3	0.5					
6										5										4									