

P-Channel Trench Power MOSFET
General Description




The JY3407AX uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as $-4.5V$. This device is suitable for use as a load switch or in PWM applications.

Features

- $V_{DS} = -30V, I_D = -4.3A$
 $R_{DS(ON)} < 50m\Omega @ V_{GS} = -10V$
 $R_{DS(ON)} < 100m\Omega @ V_{GS} = -4.5V$
- High Power and current handling capability
- Lead free product is acquired
- Surface Mount Package

Application

- PWM applications
- Load switch
- Power management


Schematic Diagram

Marking and pin Assignment

SOT23 top view
Package Marking and Ordering Information

Device Marking	Device	Device Package	Reel Size	Tape width	Quantity
3407 or JY3407	JY3407AX	SOT23	Ø180mm	8mm	3000 units

Table 1. Absolute Maximum Ratings ($T_A=25^\circ C$)

Symbol	Parameter	Value	Unit
V_{DS}	Drain-Source Voltage ($V_{GS}=0V$)	-30	V
V_{GS}	Gate-Source Voltage ($V_{DS}=0V$)	± 20	V
I_D	Drain Current-Continuous	-4.3	A
$I_{DM (pluse)}$	Drain Current-Continuous@ Current-Pulsed (Note 1)	-30	A
P_D	Maximum Power Dissipation	1.5	W
T_J, T_{STG}	Operating Junction and Storage Temperature Range	-55 To 150	$^\circ C$

Notes 1.Repetitive Rating: Pulse width limited by maximum junction temperature

Table 2. Thermal Characteristic

Symbol	Parameter	Value	Unit
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	85	$^\circ C/W$



Table 3. Electrical Characteristics (TA=25°C unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
On/Off States						
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =-250μA	-30	-34		V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} =-24V, V _{GS} =0V			1	μA
I _{GSS}	Gate-Body Leakage Current	V _{GS} =±20V, V _{DS} =0V			±100	nA
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =-250μA	-1.0	-1.6	-2.4	V
g _{FS}	Forward Transconductance	V _{DS} =-5V, I _D =-4.3A	4			S
R _{DS(ON)}	Drain-Source On-State Resistance	V _{GS} =-10V, I _D =-4.3A		38	50	mΩ
		V _{GS} =-4.5V, I _D =-4A		60	100	mΩ
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{DS} =-15V, V _{GS} =0V, f=1.0MHz		580		pF
C _{oss}	Output Capacitance			98		pF
C _{rss}	Reverse Transfer Capacitance			74		pF
Switching Times						
t _{d(on)}	Turn-on Delay Time	V _{DD} =-15V, I _D =-1A, R _L =15Ω V _{GS} =-10V, R _G =2.5Ω		5		nS
t _r	Turn-on Rise Time			6		nS
t _{d(off)}	Turn-Off Delay Time			28		nS
t _f	Turn-Off Fall Time			7		nS
Q _g	Total Gate Charge	V _{DS} =-15V, I _D =-4.3A, V _{GS} =-10V		10		nC
Q _{gs}	Gate-Source Charge			2		nC
Q _{gd}	Gate-Drain Charge			3		nC
Source-Drain Diode Characteristics						
I _{SD}	Source-Drain Current(Body Diode)				-4.3	A
V _{SD}	Forward on Voltage ^(Note 1)	V _{GS} =0V, I _S =-1A		-0.82	-1	V

Notes 1. Repetitive Rating: Pulse width limited by maximum junction temperature.







Switch Time Test Circuit and Switching Waveforms:

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS (Curves)
Figure1. Power Dissipation

Figure2. Drain Current

Figure3. Output Characteristics

Figure4. Transfer Characteristics










Figure5. Capacitance

Figure6. R_{DS(ON)} vs Junction Temperature

Figure7. Max BV_{DSS} vs Junction Temperature

Figure8. V_{GS(th)} vs Junction Temperature

Figure9. Gate Charge Waveforms

Figure10. Maximum Safe Operating Area




Figure11. Normalized Maximum Transient Thermal Impedance



SOT23 Package Information



Carrier Dimensions

PKG TYPE	W	P	E	F	D	D1	Po	Po10	P2
SOT23	8.00	4.00	1.75	3.50	1.50	1.00	4.00	40.00	2.00
Tolerance	+0.3/-0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.2	±0.05

A0	B0	K0	T
3.15	2.77	1.22	0.20
±0.1	±0.1	±0.1	±0.02

