

## Features

- ❑ Transient protection for high-speed data lines
  - IEC 61000-4-2 (ESD) ±30kV (Air)
  - ±30kV (Contact)
  - IEC 61000-4-4 (EFT) 40A (5/50 ns)
  - Cable Discharge Event (CDE)
- ❑ Package optimized for high-speed lines
- ❑ Ultra-small package (1.0mm×0.6mm×0.55mm)
- ❑ Protects one data, control or power line
- ❑ Low capacitance: 12pF (Typical)
- ❑ Low leakage current: 0.1μA @ V<sub>RWM</sub> (Typical)
- ❑ Low clamping voltage
- ❑ Each I/O pin can withstand over 1000 ESD strikes for ±8kV contact discharge
- ❑ ROHS compliant

## Description

TT0501MBX is a low-capacitance Transient Voltage Suppressor (TVS) designed to provide electrostatic discharge (ESD) protection for data, control or power lines. With typical capacitance of 12pF only, TT0501MBX is designed to protect parasitic-sensitive systems against over-voltage and over-current transient events. It complies with IEC 61000-4-2 (ESD), Level 4 (±15kV air, ±8kV contact discharge), IEC 61000-4-4 (electrical fast transient - EFT) (40A, 5/50 ns), very fast charged device model (CDM) ESD and cable discharge event (CDE), etc.

TT0501MBX uses ultra-small uDFN-2L package. Each TT0501MBX device can protect one data line. It offers system designers flexibility to protect single data line where space is a premium concern.

## Applications

- ❑ Portable Electronics
- ❑ Desktops, Servers and Notebooks
- ❑ Cellular Phones
- ❑ MP3 Ports
- ❑ Digital Camera Ports
- ❑ Subscriber Identity Module (SIM) card


## Mechanical Characteristics

- ❑ uDFN-2L package
- ❑ Flammability Rating: UL 94V-0
- ❑ Marking: Part number, date code
- ❑ Packaging: Tape and Reel

## Circuit Diagram



## Pin Configuration




uDFN-2L  
(Top View)

### Absolute Maximum Rating

Symbol	Parameter	Value	Units
$P_{PP}$	Peak Pulse Power (8/20 $\mu$ s)	48	W
$I_{PP}$	Peak Pulse Current( $t_p=8/20\mu s$ )	4	A
$V_{ESD}$	ESD per IEC 61000-4-2(Air) ESD per IEC 61000-4-2 (Contact)	$\pm 30$ $\pm 30$	kV
$T_{OPT}$	Operating Temperature	-55/+125	$^{\circ}C$
$T_{STG}$	Storage Temperature	-55/+150	$^{\circ}C$


### Electrical Characteristics (T = 25 $^{\circ}C$ )

Symbol	Parameter
$V_{RWM}$	Nominal Reverse Working Voltage
$I_R$	Reverse Leakage Current @ $V_{RWM}$
$V_{BR}$	Reverse Breakdown Voltage @ $I_T$
$I_T$	Test Current for Reverse Breakdown
$V_C$	Clamping Voltage @ $I_{PP}$
$I_{PP}$	Maximum Peak Pulse Current
$C_{ESD}$	Parasitic Capacitance
$V_R$	Reverse Voltage
f	Small Signal Frequency




Symbol	Test Condition	Minimum	Typical	Maximum	Units
$V_{RWM}$				5.0	V
$I_R$	$V_{RWM} = 5V, T = 25^{\circ}C$ Between I/O_1 and I/O_2		0.1	1.0	$\mu A$
$V_{BR}$	$I_T = 1mA$ Between I/O_1 and I/O_2	5.5	6.0	8.0	V
$V_C$	$I_{PP} = 1A, t_p = 8/20\mu s$ Between I/O_1 and I/O_2			9	V
$V_C$	$I_{PP} = 4A, t_p = 8/20\mu s$ Between I/O_1 and I/O_2			12	V
$C_{ESD}$	$V_R = 0V, f = 1MHz$ Between I/O_1 and I/O_2		12	15	pF

**TLP Measurement of I/O\_1 to I/O\_2**




**Voltage Sweeping of I/O\_1 to I/O\_2**




**Capacitance vs. Voltage of I/O\_1 to I/O\_2 (f = 1MHz)**


Capacitance vs. Reverse Voltage




Normalized Capacitance vs. Reverse Voltage



**ESD Clamping of I/O\_1 to I/O\_2  
(+8kV Contact per IEC 61000-4-2)**




**ESD Clamping of I/O\_1 to I/O\_2  
(-8kV Contact per IEC 61000-4-2)**





### Package Outline


- ❑ uDFN-2L package
- ❑ 2 leads, very small package
- ❑ MSL-1




Package Dimensions (Controlling dimensions are in millimeters)

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Minimum	Maximum	Minimum	Maximum
A	0.400	0.550	0.016	0.022
A1	0.000	0.050	0.000	0.002
A3	0.125 REF		0.005 REF	
D	0.950	1.050	0.037	0.041
E	0.550	0.650	0.022	0.026
b	0.200	0.300	0.008	0.012
e	0.650 BSC		0.026 BSC	
L	0.450	0.550	0.018	0.022

### Tape and Reel Specification



Symbol	W	A0	B0	K0	E	F	P	P0	P2	T
Dimensions (mm)	8.00±0.1	0.7±0.05	1.15±0.05	0.55±0.05	1.75±0.1	3.5±0.05	2.0±0.1	4.0±0.1	2.0±0.05	0.2±0.05



Symbol	Reel Size	M	N	W	W1	H	S	K	R
Dimensions (mm)	Φ178	178.0±1.0	60.0±1.0	11.5±0.5	9.0±0.5	13.0±0.5	2.0±0.1	11.0±0.2	1.0±0.05



### Marking Codes



└ Pin1 Identification

### Ordering Information

Part Number	Working Voltage	Quantity Per Reel	Reel Size
TT0501MBX	5V	10,000	7 Inch

Note:

- (1) “F” is part number, fixed
- (2) “M” is date code, which is the assembly month in three years, changing as (1~9, 0, A~Z)