






SCHEMATIC



SPECIFICATION

1. Rating : DC12V 50mA.
2. Contact resistance: $\leq 100\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
4. Withstanding voltage: 250VAC .
5. Operating Force: $250\pm 80\text{gf}$
6. Travel: $0.25\pm 0.1\text{mm}$.
7. life test: 5,0000 cycles.
8. Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
9. Sign"* "is importance dimension.

TEL:0769-82310510-867



P.C.B LAYOUT

H=6.0mm

					TOLERANCE UNLESS SPECIFIED								
					< 1. 5: ±0. 1mm > 1. 5~5. 0: ±0. 25mm > 5. 0: ±0. 3mm	ANGULAR ±1°	1						
5	STEM	PPA	1	BLACK			NO	DATE	REVISIONS			BY	APPD
4	COVER	SUS	1	WHITE	TITLE: SLIDE SWITCH				UNIT : MM	ROHS	DWN		
3	CONTACT	SUS	1	Ag-Plated	MODEL: TC-06121-060E-01				SCALE: 1:1	COMPLIANT	CHK'D		
2	CASE	PPA	1	BLACK	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD				
1	TERMINAL	BRASS	4	Ag-Plated									
NO.	PART	NAME	MATERIAL	QTY	FINISHING					PRO.AGL: 		REV :A1	