

# 承 認 書

## PRODUCT APPROVAL SHEET

产品名称 PRODUCT Name : 轻触开关

规格型号 PART NO : 12\*12 防水插脚

物 料 号 PART NO :

|                  |                  |                  |  |
|------------------|------------------|------------------|--|
| 制表/DESIGNED BY   | 校对/CHECKED BY    | 审核/APPROVED BY   |  |
| 吴永余              | 吴永友              | 张 鹏              |  |
| DATE 日期 20201117 | DATE 日期 20201117 | DATE 日期 20201117 |  |

贵司承认栏 APPROVAL SIGNATURE

贵司名称/CUSTOMER NAME:

贵司物料名称/CUSTOMER TYPE:

贵司物料号/CUSTOMER NO:


请于\_\_\_\_\_年\_\_\_\_\_月\_\_\_\_\_日前承认返 日期 DATE:

PLEASE RETURN TO US AFTER CONFIRMED! THANK YOU!




|       |              |      |       |             |
|-------|--------------|------|-------|-------------|
| ISSUE | DATE         | WRTN | CHKD  | Page 1 of 7 |
| 001   | 2020. 11. 17 | WU   | ZHANG |             |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |            |      |       |             |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|------|-------|-------------|
| 深圳市金航标电子有限公司                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |            |      | 产品系列  | 轻触开关        |
| TACT SWITCH SPECIFICATION<br>轻触开关产品承认书                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |            |      |       |             |
| <p>1、概述 GENERAL</p> <p>1.1 适用范围 APPLICATION</p> <p>此规格书适用于机械式轻触开关的相关要求</p> <p>This specification is applied to the requirements for TACTILE SWITCH(MECHANICAL CONTACT)</p> <p>1.2 工作温度范围</p> <p>Operating Temperature Range</p> <p>-20℃~70℃ (在标准大气压、标准温度条件下)</p> <p>-20℃~70℃ (Normal humidity, normal air pressure)</p> <p>1.3 贮藏温度范围</p> <p>Storage Temperature Rane</p> <p>-40℃~85℃ (在标准大气压、标准温度条件下)</p> <p>-40℃~85℃ (Normal humidity, normal air pressure)</p> <p>1.4 测试条件</p> <p>Test Conditions</p> <p>在没有其它特定的条件下，应该在以下的条件下进行测试和测量：</p> <p>Unless otherwise specified, tests and measurement shall be made in the following standard conditions</p> <p>常温.....5℃~35℃</p> <p>Normal temperature.....5℃~35℃</p> <p>标准湿度.....相对湿度 45%~85%</p> <p>Normal humidity.....relative humidity 45%~85%</p> <p>标准大气压.....86KPa~106 KPa</p> <p>Normal air pressure.....86KPa~106 KPa</p> <p>在制造过程中，测试和测量应该在以下的条件下进行：</p> <p>If any doubt arise from the judgment, tests shall be conducted at the following conditions</p> <p>温度.....20℃±2℃</p> <p>Temperature.....20℃±2℃</p> <p>相对湿度.....65%±5%</p> <p>Relative humidity.....65%±5%</p> <p>环境气压.....86KPa~106 KPa</p> <p>Air pressure.....86KPa~106 KPa</p> <p>2、详细说明 Detailed specification</p> <p>2.1 外观：应无影响、降低产品性能的缺陷</p> <p>Appearance:There should be no defects that affect the serviceability of product.</p> <p>2.2 结构尺寸和安装尺寸：应符合装配图要求</p> <p>Style and dimension:shall conform to the assemble drawings.</p> |            |      |       |             |
| ISSUE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            | DATE       | WRTN | CHKD  | Page 2 of 7 |
| 001                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              | 2020.11.17 | WU   | ZHANG |             |

|                                                                                                                                                                                                                                                                  |            |                                                                                      |       |             |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------|--------------------------------------------------------------------------------------|-------|-------------|
| 深圳市金航标电子有限公司                                                                                                                                                                                                                                                     |            |                                                                                      | 产品系列  | 轻触开关        |
| TACT SWITCH SPECIFICATION<br>轻触开关产品承认书                                                                                                                                                                                                                           |            |                                                                                      |       |             |
| 2.3 操作形式：有触觉反应的操作<br>Type of actuating:Tactile feedback.<br>2.4 开关结构：单回路输出（具体的触点结构在装配图中已绘出）<br>Contact arrangement:1 pole,1 throw<br>(Details of contact arrangement are given in the assembly drawings.)<br>2.5 开关工作额定值：DC12V 50mA<br>Ratings: DC12V 50mA       |            |                                                                                      |       |             |
| 测试项目 TEST ITEM                                                                                                                                                                                                                                                   |            |                                                                                      |       |             |
| 3. 电器性能 ELECTRICAL PERFORMANCE                                                                                                                                                                                                                                   |            |                                                                                      |       |             |
| 3-1 接触电阻 CONTACT RESISTANCE<br>在 1kHz 小电流电压（50mA，20mV）下测量。<br>Being tested at 1kHz small current and voltage (50mA，20mV) by contact resistance meter.<br>100 毫欧以下。<br>100mΩ max.                                                                                 |            |                                                                                      |       |             |
| 3-2 绝缘电阻 INSULATION RESISTANCE<br>在端子之间和端子与壳之间加 DC250V 条件下，持续 1 分钟测量。<br>DC 250v shall be applied for test between terminals and between terminals and frame for one minute.<br>100 兆欧以上。<br>100MΩ min.                                                          |            |                                                                                      |       |             |
| 3-3 耐电压 WITHSTAND VOLTAGE<br>在端子之间和端子于壳之间加 AC250V（50Hz 或 60Hz）感应电流 1mA 条件下，持续 1 分钟测量。<br>AC 250V and induction current 1mA shall be applied for test between terminals and between terminals and frame for one minute.<br>无击穿现象。<br>There shall be no breakdown. |            |                                                                                      |       |             |
| 4. 机械性能 MECHANICAL PERFORMANCE                                                                                                                                                                                                                                   |            |                                                                                      |       |             |
| 4-1 动作力 OPERATING FORCE<br><br>260±50gf                                                                                                                                                                                                                          |            |  |       |             |
| ISSUE                                                                                                                                                                                                                                                            | DATE       | WRTN                                                                                 | CHKD  | Page 3 of 7 |
| 001                                                                                                                                                                                                                                                              | 2020.11.17 | WU                                                                                   | ZHANG |             |

[illegible]

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |              |                                                                   |       |             |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|-------------------------------------------------------------------|-------|-------------|
| 深圳市金航标电子有限公司                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |              | 产品系列                                                              | 轻触开关  |             |
| TACT SWITCH SPECIFICATION<br>轻触开关产品承认书                                                                                                                                                                                                                                                                                                                                                                                                                                                     |              |                                                                   |       |             |
| 5. 耐久性 DURABILITY                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |              |                                                                   |       |             |
| 5-1 可焊性试验 SOLDERING TEST                                                                                                                                                                                                                                                                                                                                                                                                                                                                   |              |                                                                   |       |             |
| <p>端子顶部被侵入锡池 0.5mm 深，温度 260±5℃，时间 3 秒。</p> <p>The tip of the terminal shall be dipped 0.5mm in the solder bath within temperature of 260±5℃ for 3s.</p> <p>侵入的部分 95%以上表面将被锡覆盖</p> <p>Over 95% of the immersed surface was covered by tin .</p>                                                                                                                                                                                                                                             |              |                                                                   |       |             |
| 5-2 耐焊性试验 SOLDERING RESISTANT TEST                                                                                                                                                                                                                                                                                                                                                                                                                                                         |              |                                                                   |       |             |
| <p>焊炉锡的温度控制在 260±5℃，时间为 3±0.5 秒, 与(基板)厚度 1.6mm.</p> <p>Soldering temperature 260±5℃, soldering time 3±0.5s, immersion depth up to the surface of the board, thickness of PCB 1.6mm.</p> <p>手焊接时温度控制在 350±5℃，时间为 3±0.5 秒，但不能在端子上施加异常压力。</p> <p>Manual soldering temperature350±5℃, soldering time 3±0.5s,however excessive pressure shall not be applied to the terminal.</p> <p>本体无变形, 能满足与机械、电器性能。</p> <p>Without deformation of case or excessive looseness of electrical properties</p> |              |                                                                   |       |             |
| 5-3 波峰焊接熱試驗 WAVE SOLDERING HEAR TEST                                                                                                                                                                                                                                                                                                                                                                                                                                                       |              |                                                                   |       |             |
| <p>本体无变形, 能满足与机械、电器性能。</p> <p>Without deformation of case or excessive looseness of electrical properties</p>                                                                                                                                                                                                                                                                                                                                                                              |              | <p>Time inside soldering equipment</p> <p>Temperature Profile</p> |       |             |
| ISSUE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      | DATE         | WRTN                                                              | CHKD  | Page 5 of 7 |
| 001                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        | 2020. 11. 17 | WU                                                                | ZHANG |             |

|                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |              |      |       |                                                                                                                                                                                                                                                                                                             |      |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------|------|-------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------|
| 深圳市金航标电子有限公司                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |              |      |       | 产品系列                                                                                                                                                                                                                                                                                                        | 轻触开关 |
| TACT SWITCH SPECIFICATION<br>轻触开关产品承认书                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |              |      |       |                                                                                                                                                                                                                                                                                                             |      |
| <p>5-4 寿命测试 LIFE TEST</p> <p>无负载条件, 每分钟 100-120 次的速度操作 50,000 次。</p> <p>50,000cycles of operation at a rate of 100-120 cycles per minute with unloading</p> <p>(1) 接触电阻 200 毫欧以下。Contact resistance 200mΩ</p> <p>(2) 动作力变化范围初始值 30%。Operating force 30% initial value.</p> <p>(3) ITEM 项目——1.2</p> <p>(4) ITEM 项目——1.3</p> <p>(5) ITEM 项目——2.2</p>                                                                                                                                                                                                                                                                                                                                                              |              |      |       |                                                                                                                                                                                                                                                                                                             |      |
| <p>5-5 盐雾 SAIL SPRA</p> <p>1) 测试温度: 35±2℃ Temperature: 35±2℃</p> <p>2) 循环次数: 4 小时喷雾 1 小时停, 连续 1 次。喷雾 4 小时。Cycle: 4 Hours testing(1Times) and 1 Hours stop. Based on total 4 hours.</p> <p>3) 盐雾浓度: 5±1% Salt solution concentration: 5±1% by weight.</p> <p>(1) 接触电阻 200 毫欧以下。Contact resistance 200mΩ.</p> <p>(2) 绝缘电阻 100 兆欧以上。Insulation resistance 100MΩ min.</p> <p>(3) 无任何迹象显示机械及电器性能之损坏</p> <p>there shall be no sign of mechanical and electrical damage.</p>                                                                                                                                                                                                                                           |              |      |       |                                                                                                                                                                                                                                                                                                             |      |
| <p>5-6 耐热试验 HEAT RESISTAN TEST</p> <p>在 80±2℃ 环境中放 96 小时, 再置于正常环境中, 30 分钟后进行测试。</p> <p>80±2℃ for 96H, test after keeping in normal condition for 30min.</p> <p>5-7 耐湿试验 MOISTURE RESISTANT TEST</p> <p>在 60±2℃ 90~95% 环境中放 96 小时, 再置于正常环境中, 30 分钟后进行测试。</p> <p>At 60±2℃ 90~95% RH for 96H, test after keeping in normal condition for 30min.</p> <p>5-8 耐冷试验 COLD RESISTANT TEST</p> <p>在 -40±2℃ 环境中放 96 小时, 再置于正常环境中, 30 分钟后进行测试。</p> <p>At -40±2℃ for 96H, test after keeping in normal condition for 30min.</p> <p>5-9 温度交变试验 TEMPERATURE CYCLIG TEST</p> <p>如图示之环境中, 循环 5 次后, 再置于正常环境中, 1 个小时后进行测试。</p> <p>According to following figure, after 5cycles, test after keeping in normal condition for 1H.</p> |              |      |       |  <p>(1) 接触电阻 200 毫欧以下。<br/>Contact resistance 200mΩ.</p> <p>(2) 绝缘电阻 100 兆欧以上。<br/>insulation resistance 100MΩ min.</p> <p>(3) 无任何迹象显示机械及电器性能之损坏</p> <p>there shall be no sign of mechanical and electrical damage.</p> |      |
| ISSUE                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           | DATE         | WRTN | CHKD  | Page 6 of 7                                                                                                                                                                                                                                                                                                 |      |
| 001                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             | 2020. 11. 17 | WU   | ZHANG |                                                                                                                                                                                                                                                                                                             |      |

