

## Features

- Transient protection for high-speed data lines
  - IEC 61000-4-2 (ESD) ±17kV (Air)
  - ±8 kV (Contact)
- IEC 61000-4-4 (EFT) 40A (5/50 ns)
- Cable Discharge Event (CDE)
- Package optimized for high-speed lines
- Ultra-small package (1.0mm×0.6mm×0.55mm)
- Protects one data, control or power line
- Low capacitance: 0.6pF (Typical)
- Low leakage current: 0.1μA @ V<sub>RWM</sub> (Typical)
- Low clamping voltage
- Each I/O pin can withstand over 1000 ESD strikes for ±8kV contact discharge
- ROHS compliant

## Description

TT0311TBX is an ultra low-capacitance Transient Voltage Suppressor (TVS) designed to provide electrostatic discharge (ESD) protection for high-speed data interfaces. With typical capacitance of 0.6pF only, TT0311TB is designed to protect parasitic-sensitive systems against over-voltage and over-current transient events. It complies with IEC 61000-4-2 (ESD (±17kV air, ±8 kV contact discharge), IEC 61000-4-4 (electrical fast transient - EFT) (40A, 5/50 ns), very fast charged device model (CDM) ESD and cable discharge event (CDE), etc.

TT0311TB uses ultra-small uDFN-2L package. Each TT0311TB device can protect one high-speed data line. It offers system designers flexibility to protect single data line where space is a premium concern. The combined features of low capacitance, ultra-small size and high ESD robustness make TT0311TB ideal for high-speed data port and high-frequency line (e.g. HDMI & antenna line) applications, such as cellular phones and HD visual devices.


## Applications

- Serial ATA
- PCI Express
- Desktops, Servers and Notebooks
- Cellular Phones
- MDDI Ports
- USB2.0/3.0 Power and Data Line Protection
- Display Ports
- High Definition Multi-Media Interface (HDMI)
- Digital Visual Interfaces (DVI)


## Mechanical Characteristics

- uDFN-2L package
- Flammability Rating: UL 94V-0
- Marking: Part number
- Packaging: Tape and Reel

## Circuit Diagram



## Pin Configuration




uDFN-2L  
(Top View)

## Absolute Maximum Rating

Symbol	Parameter	Value	Units
I <sub>PP</sub>	Peak Pulse Current(tp=8/20us)	5	A
V <sub>ESD</sub>	ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	±17 ±8	kV
T <sub>OPT</sub>	Operating Temperature	-55/+125	°C
T <sub>STG</sub>	Storage Temperature	-55/+150	°C


## Electrical Characteristics (T = 25°C)

Symbol	Parameter
V <sub>RWM</sub>	Nominal Reverse Working Voltage
I <sub>R</sub>	Reverse Leakage Current @ V <sub>RWM</sub>
V <sub>t1</sub>	Trigger Voltage
I <sub>t1</sub>	Trigger Current @ V <sub>t1</sub>
V <sub>h</sub>	Holding Voltage
I <sub>h</sub>	Holding Current @ V <sub>h</sub>
V <sub>C</sub>	Clamping Voltage @ I <sub>PP</sub>
I <sub>PP</sub>	Maximum Peak Pulse Current
V <sub>F</sub>	Forward Voltage @ I <sub>F</sub>
C <sub>ESD</sub>	Parasitic Capacitance




Symbol	Test Condition	Minimum	Typical	Maximum	Units
V <sub>RWM</sub>				3.3	V
I <sub>R</sub>	V <sub>RWM</sub> = 3.3V, T = 25°C Between I/O and GND			0.1	µA
V <sub>t1</sub>	I <sub>T</sub> = 1mA Between I/O and GND	6.0		10.0	V
V <sub>h</sub>	I <sub>h</sub> = 40mA Between I/O and GND	1.5		3.0	V
V <sub>C</sub>	I <sub>PP</sub> = 5A, t <sub>p</sub> = 8/20µs Between I/O and GND			5.0	V
C <sub>ESD</sub>	V <sub>R</sub> = 0V, f = 1MHz Between I/O and GND		0.6	0.7	pF

### TLP Measurement of I/O to GND




### Capacitance vs. Voltage of I/O to GND ( $f = 1\text{MHz}$ )


Capacitance vs. Reverse Voltage




Normalized Capacitance vs. Reverse Voltage



### ESD Clamping of I/O to GND (+8kV Contact per IEC 61000-4-2)




### ESD Clamping of I/O to GND (-8kV Contact per IEC 61000-4-2)



## Package Outline


- uDFN-2L package
- 2 leads, very small package
- MSL-1



Package Dimensions (Controlling dimensions are in millimeters)


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Minimum	Maximum	Minimum	Maximum
A	0.400	0.550	0.016	0.022
A1	0.000	0.050	0.000	0.002
A3	0.125 REF		0.005 REF	
D	0.950	1.050	0.037	0.041
E	0.550	0.650	0.022	0.026
b	0.200	0.300	0.008	0.012
e	0.650 BSC		0.026 BSC	
L	0.450	0.550	0.018	0.022

## Tape and Reel Specification



Symbol	W	A0	B0	K0	E	F	P	P0	P2	T
Dimensions (mm)	8.00±0.1	0.7±0.05	1.15±0.05	0.55±0.05	1.75±0.1	3.5±0.05	2.0±0.1	4.0±0.1	2.0±0.05	0.2±0.05

## Marking Codes



## Ordering Information

Part Number	Working Voltage	Quantity Per Reel	Reel Size
TT0311TBX	3.3V	10,000	7 Inch

### Note:

- (1) "T" is part number, fixed
- (2) "X" is internal code.