

Features

- ❑ IEC61000-4-2 (ESD) +/-30kV (air),
 +/-30KV(contact)
- IEC61000-4-4 (EFT) 40A (5/50ns)
- IEC61000-4-5 (EOS) (1.2/50uS, 8/20uS)
- ❑ Protects one I/O line (bidirectional)
- ❑ Working voltages : 3.3V,8V,12V,15V,18V,
 24V,36V
- ❑ Low leakage current
- ❑ ROHS compliant

Description

The TSxx01TEX Series are ultra low capacitance transient voltage suppressor arrays, designed to protect applications such as portable electronics and SMART phones. The TSxx01TEX and Series meets IEC 61000-4-2 (ESD) and IEC 61000-4-4 (EFT) requirements. At higher operating frequencies or faster edge rates, insertion loss and signal integrity are a major concern. This series offers a ultra low capacitance and low leakage current in a miniature SOD323 package.

Applications

- ❑ Cell Phone Handsets and Accessories
- ❑ Microprocessor based equipment
- ❑ Personal Digital Assistants (PDA's)
- ❑ Notebooks, Desktops, and Servers
- ❑ Portable Instrumentation
- ❑ Peripherals
- ❑ USB Interface


Mechanical Characteristics

- ❑ SOD323 package
- ❑ Flammability Rating: UL 94V-0
- ❑ Packaging:Tape and Reel
- ❑ High temperature soldering guaranteed:260°C/10s
- ❑ Reel size: 7 inch

Ordering Information

- Device: TSxx01TEX
- ❑ Package: SOD323
 - ❑ Material: Halogen free
 - ❑ Packing: Tape & Reel
 - ❑ Quantity per reel: 3,000pcs

Pin Configuration



(Top View)


Absolute Maximum Rating

Symbol	Parameter	Value	Units
V_{ESD}	ESD per IEC 61000-4-2 (Air)	± 30	kV
	ESD per IEC 61000-4-2 (Contact)	± 30	
T_{OPT}	Operating Temperature	-55 to +150	°C
T_{STG}	Storage Temperature	-55 to +150	°C
T_{LST}	Lead Soldering Temperature	260	°C


Electrical Characteristics (T = 25°C)

PART NUMBER	DEVICE MARKING	V_{RWM} (V) (max.)	V_B (V) (min.)	I_{pp} (A) (max.)	$V_{C@1A}$ (V) (max.)	V_C (V) (max.) (@A)		I_R (nA) (max.)	C_T (pF) (typ.)
TS0301TEX	AC/CC	3.3	4.0	20	8.0	16	20	50	0.9
TS0801TEX	BC	8.0	9.2	15	15.0	28	15	50	0.9
TS1201TEX	DC	12.0	13.3	13	19.0	32	13	50	0.9
TS1501TEX	EC	15.0	16.7	10	24.0	36	10	50	0.9
TS1801TEX	GC	18.0	20.0	8	28.0	45	8	50	0.9
TS2401TEX	HC	24.0	26.7	7	36.0	50	7	50	0.9
TS3601TEX	KC	36.0	40.0	6	50.0	60	6	50	0.9


Electrical Characteristics Curve










Pulse Waveform



Non-Repetitive Peak Pulse Power vs. Pulse Time



Power Derating Curve


IEC61000-4-5 EOS Test (1.2/50uS, 8/20uS)
TS0301TEX

TS0801TEX

TS1201TEX

TS1501TEX

TS1801TEX

TS2401TEX

TS3601TEX


Package Outline


□ SOD323 package



Package Outline Dimensions




Symbol	Dimensions In Millimeters	
	Min	Max
A		1.00
A1	0.000	0.100
A2	0.800	0.900
b	0.250	0.350
c	0.080	0.150
D	1.200	1.400
E	1.600	1.800
E1	2.500	2.700
e	1.800	2.040
L	0.475 REF	
L1	0.250	0.400
θ	0°	8°



Recommended Pad outline


P.S. TSxx01TEX series are the bidirectional TVS. The device marking is directionless. Then the device orientation in tape is not requested.

Tape and Reel Specification




Dimensions are in millimeter										
Pkg type	A	B	C	d	E	F	P0	P	P1	W
SOD-323	1.46	2.90	1.25	Ø1.50	1.75	3.50	4.00	4.00	2.00	8.00
(Tolerance)	+/-0.05	+/-0.05	+/-0.05	+/-0.1	+/-0.1	+/-0.1	+/-0.1	+/-0.1	+/-0.1	+0.3/-0.1

SOD-323 Tape Leader and Trailer



SOD-323 Reel



Dimensions are in millimeter								
Reel Option	D	D1	D2	G	H	I	W1	W2
7" Dia	Ø178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30
Tolerance	+/-2	+/-1	+/-1	+/-1	+/-1	+/-1	+/-1	+/-1

REEL	Reel Size	Box	Box Size(mm)	Carton	Carton Size(mm)	G.W.(kg)
3000 pcs	7 inch	45,000 pcs	203×203×195	180,000 pcs	438×438×220	