






Technical Index:

1. Temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
2. Rated voltage: 250V DC/AC(rms).
3. Rated current: 7.0A.
4. Contact resistance: $\leq 20\text{m}\Omega$.
5. Withstanding voltage: 1500V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.



通用线路板(PCB LAYOUT)



Part No	Pin	A	B
XY-VH3.96-2A21-R	2	3.96	7.92
XY-VH3.96-3A21-R	3	7.92	11.88
XY-VH3.96-4A21-R	4	11.88	15.84
XY-VH3.96-5A21-R	5	15.84	19.80
XY-VH3.96-6A21-R	6	19.80	23.76
XY-VH3.96-7A21-R	7	23.76	27.72
XY-VH3.96-8A21-R	8	27.72	31.68
XY-VH3.96-9A21-R	9	31.68	35.64
XY-VH3.96-10A21-R	10	35.64	39.60
XY-VH3.96-11A21-R	11	39.60	43.56
XY-VH3.96-12A21-R	12	43.56	47.52
XY-VH3.96-13A21-R	13	47.52	51.48
XY-VH3.96-14A21-R	14	51.48	55.44
XY-VH3.96-15A21-R	15	55.44	59.40
XY-VH3.96-16A21-R	16	59.40	63.36

序号	品名	材质
1	基座Wafer	PA66 UL94V-2 红色
2	端子Contact	铜合金/镀锡

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.35	X.*±5°	APR. Alex	TITLE: WAFER 3.96 90° DIP 红色		
.XX±0.25	.X.*±3°	CHK. Jack	DWG NO. XY-VH3.96-NA21-R		
.XXX±0.15	.XX.*±1°	DRA. Can	PROJ.	CUSTOMER DRAWING	
		SIZE A4	SCALE 1:1	SHEET 1/1	REV. A