



CD4001 (LX) Quad 2-input Nor Gate

Product Specification

Specification Revision History:

| Version | Date | Description |
|------------|---------|-------------|
| 2021-12-A1 | 2021-12 | New |
| | | |
| | | |



1、General Description

The CD4001 is a quad 2-input NOR gate. The outputs are fully buffered for the highest noise immunity and pattern insensitivity to output impedance.

It operates over a recommended V_{DD} power supply range of 3V to 15V referenced to V_{SS} (usually ground).

Unused inputs must be connected to V_{DD} , V_{SS} , or another input.

Features:

- Wide supply voltage range from 3V to 15V
- Fully static operation
- 5V, 10V, and 15V parametric ratings
- Standardized symmetrical output characteristics
- Inputs and outputs are protected against electrostatic effects
- Specified from -40°C to $+85^{\circ}\text{C}$
- Packaging information: DIP14/SOP14/TSSOP14

Ordering Information:

Tube packing specifications:

| Type number | Packaging form | Marking code | Tube quantity | Boxed tube quantity | Boxed quantity | Packing box number | Packing quantity | Notes |
|--------------|----------------|--------------|----------------|---------------------|-----------------|--------------------|-------------------|-------------------------------------------------------------------------|
| CD4001BE(LX) | DIP14 | CD4001BE | 25 PCS/tube | 40 tube/box | 1000 PCS/box | 10 box/pack | 10000 PCS/pack | Dimensions of plastic enclosure: 19.0mm×6.4mm Pin spacing: 2.54mm |

Reel packing specifications:

| Type number | Packaging form | Marking code | Reel quantity | Boxed reel quantity | Packing quantity | Notes |
|---------------|----------------|--------------|------------------|---------------------|-------------------|------------------------------------------------------------------------|
| CD4001BM(LX) | SOP14 | CD4001BM | 4000 PCS/reel | 8000 PCS/box | 64000 PCS/pack | Dimensions of plastic enclosure: 8.7mm×3.9mm Pin spacing: 1.27mm |
| CD4001BPW(LX) | TSSOP14 | CD4001 | 5000 PCS/reel | 10000 PCS/box | 80000 PCS/pack | Dimensions of plastic enclosure: 5.0mm×4.4mm Pin spacing: 0.65mm |

Note: If the physical information is inconsistent with the ordering information, please refer to the actual product.



2、Block Diagram And Pin Description

2.1、Block Diagram




Figure 1. Functional diagram





Figure 2. Logic diagram (one gate)

2.2、Pin Configurations





2.3、Pin Description

| Pin No. | Pin Name | Description |
|---------|-----------------|----------------|
| 1 | 1A | data input |
| 2 | 1B | data input |
| 3 | 1Y | data output |
| 4 | 2Y | data output |
| 5 | 2A | data input |
| 6 | 2B | data input |
| 7 | V _{SS} | ground (0V) |
| 8 | 3A | data input |
| 9 | 3B | data input |
| 10 | 3Y | data output |
| 11 | 4Y | data output |
| 12 | 4A | data input |
| 13 | 4B | data input |
| 14 | V _{DD} | supply voltage |

2.4、Function Table

| Input | | Output |
|-------|----|--------|
| nA | nB | nY |
| L | L | H |
| L | H | L |
| H | L | L |
| H | H | L |

Note: H=HIGH voltage level; L=LOW voltage level.

3、Electrical Parameter

3.1、Absolute Maximum Ratings

(Voltages are referenced to V_{SS} (ground=0V), unless otherwise specified.)

| Parameter | Symbol | Conditions | Min. | Max. | Unit |
|-------------------------|------------------|-----------------------|------|----------------------|------|
| supply voltage | V _{DD} | - | -0.5 | +18 | V |
| DC input current | I _{IK} | any one input | - | ±10 | mA |
| input voltage | V _I | all inputs | -0.5 | V _{DD} +0.5 | V |
| storage temperature | T _{stg} | - | -65 | +150 | °C |
| total power dissipation | P _{tot} | - | - | 500 | mW |
| device dissipation | P | per output transistor | - | 100 | mW |
| Soldering temperature | T _L | 10s | DIP | 245 | °C |
| | | | SOP | 250 | °C |

Note:

[1] For DIP14 packages: above 70°C the value of P_{tot} derates linearly with 12mW/K.

[2] For SOP14 packages: above 70°C the value of P_{tot} derates linearly with 8mW/K.

[3] For (T)SSOP14 packages: above 60°C the value of P_{tot} derates linearly with 5.5mW/K.



3.2、Recommended Operating Conditions

| Parameter | Symbol | Conditions | Min. | Typ. | Max. | Unit |
|---------------------|-----------|-------------|------|------|------|------|
| supply voltage | V_{DD} | - | 3 | - | 15 | V |
| ambient temperature | T_{amb} | in free air | -40 | - | +85 | °C |

3.3、Electrical Characteristics

3.3.1、DC Characteristics 1

($T_{amb}=25^{\circ}\text{C}$, voltages are referenced to V_{SS} (ground=0V), unless otherwise specified.)

| Parameter | Symbol | Conditions (V) | | | $T_{amb}=25^{\circ}\text{C}$ | | | Unit |
|---------------------------|----------|----------------|----------|----------|------------------------------|---------------|-----------|------|
| | | V_O | V_{IN} | V_{DD} | Min. | Typ. | Max. | |
| supply current | I_{DD} | - | 0, 5 | 5 | - | 0.01 | 0.25 | uA |
| | | - | 0, 10 | 10 | - | 0.01 | 0.5 | uA |
| | | - | 0, 15 | 15 | - | 0.01 | 1 | uA |
| LOW-level output current | I_{OL} | 0.4 | 0, 5 | 5 | 0.51 | 1 | - | mA |
| | | 0.5 | 0, 10 | 10 | 1.3 | 2.6 | - | mA |
| | | 1.5 | 0, 15 | 15 | 3.4 | 6.8 | - | mA |
| HIGH-level output current | I_{OH} | 4.6 | 0, 5 | 5 | -0.51 | -1 | - | mA |
| | | 2.5 | 0, 5 | 5 | -1.6 | -3.2 | - | mA |
| | | 9.5 | 0, 10 | 10 | -1.3 | -2.6 | - | mA |
| | | 13.5 | 0, 15 | 15 | -3.4 | -6.8 | - | mA |
| LOW-level output voltage | V_{OL} | - | 0, 5 | 5 | - | 0 | 0.05 | V |
| | | - | 0, 10 | 10 | - | 0 | 0.05 | V |
| | | - | 0, 15 | 15 | - | 0 | 0.05 | V |
| HIGH-level output voltage | V_{OH} | - | 0, 5 | 5 | 4.95 | 5 | - | V |
| | | - | 0, 10 | 10 | 9.95 | 10 | - | V |
| | | - | 0, 15 | 15 | 14.95 | 15 | - | V |
| LOW-level input voltage | V_{IL} | 0.5, 4.5 | - | 5 | - | - | 1.5 | V |
| | | 1, 9 | - | 10 | - | - | 3 | V |
| | | 1.5, 13.5 | - | 15 | - | - | 4 | V |
| HIGH-level input voltage | V_{IH} | 0.5 | - | 5 | 3.5 | - | - | V |
| | | 1 | - | 10 | 7 | - | - | V |
| | | 1.5 | - | 15 | 11 | - | - | V |
| input leakage current | I_I | - | 0, 15 | 15 | - | $\pm 10^{-5}$ | ± 0.1 | uA |



3.3.2 、 DC Characteristics 2

($T_{amb}=-40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$, voltages are referenced to V_{SS} (ground=0V), unless otherwise specified.)

| Parameter | Symbol | Conditions (V) | | | $T_{amb}=-40^{\circ}\text{C}$ | | $T_{amb}=+85^{\circ}\text{C}$ | | Unit |
|---------------------------|----------|----------------|----------|----------|-------------------------------|-----------|-------------------------------|---------|---------------|
| | | V_O | V_{IN} | V_{DD} | Min. | Max. | Min. | Max. | |
| supply current | I_{DD} | - | 0, 5 | 5 | - | 0.25 | - | 7.5 | μA |
| | | - | 0, 10 | 10 | - | 0.5 | - | 15 | μA |
| | | - | 0, 15 | 15 | - | 1 | - | 30 | μA |
| LOW-level output current | I_{OL} | 0.4 | 0, 5 | 5 | 0.61 | - | 0.42 | - | mA |
| | | 0.5 | 0, 10 | 10 | 1.5 | - | 1.1 | - | mA |
| | | 1.5 | 0, 15 | 15 | 4 | - | 2.8 | - | mA |
| HIGH-level output current | I_{OH} | 4.6 | 0, 5 | 5 | -0.61 | - | -0.42 | - | mA |
| | | 2.5 | 0, 5 | 5 | -1.8 | - | -1.3 | - | mA |
| | | 9.5 | 0, 10 | 10 | -1.5 | - | -1.1 | - | mA |
| | | 13.5 | 0, 15 | 15 | -4 | - | -2.8 | - | mA |
| LOW-level output voltage | V_{OL} | - | 0, 5 | 5 | - | 0.05 | - | 0.05 | V |
| | | - | 0, 10 | 10 | - | 0.05 | - | 0.05 | V |
| | | - | 0, 15 | 15 | - | 0.05 | - | 0.05 | V |
| HIGH-level output voltage | V_{OH} | - | 0, 5 | 5 | 4.95 | - | 4.95 | - | V |
| | | - | 0, 10 | 10 | 9.95 | - | 9.95 | - | V |
| | | - | 0, 15 | 15 | 14.95 | - | 14.95 | - | V |
| LOW-level input voltage | V_{IL} | 0.5, 4.5 | - | 5 | - | 1.5 | - | 1.5 | V |
| | | 1, 9 | - | 10 | - | 3 | - | 3 | V |
| | | 1.5, 13.5 | - | 15 | - | 4 | - | 4 | V |
| HIGH-level input voltage | V_{IH} | 0.5 | - | 5 | 3.5 | - | 3.5 | - | V |
| | | 1 | - | 10 | 7 | - | 7 | - | V |
| | | 1.5 | - | 15 | 11 | - | 11 | - | V |
| input leakage current | I_I | - | 0, 15 | 15 | - | ± 0.1 | - | ± 1 | μA |

3.3.3 、 AC Characteristics

($T_{amb}=25^{\circ}\text{C}$, $V_{SS}=0\text{V}$, $t_r, t_f=20\text{ns}$, $C_L=50\text{pF}$, $R_L=200\text{k}\Omega$, unless otherwise specified.)

| Parameter | Symbol | Conditions | Min. | Typ. | Max. | Unit |
|------------------------|--------------------|---------------------|------|------|------|------|
| propagation delay time | t_{PHL}, t_{PLH} | $V_{DD}=5\text{V}$ | - | 125 | 250 | ns |
| | | $V_{DD}=10\text{V}$ | - | 60 | 120 | ns |
| | | $V_{DD}=15\text{V}$ | - | 45 | 90 | ns |
| transition time | t_{THL}, t_{TLH} | $V_{DD}=5\text{V}$ | - | 100 | 200 | ns |
| | | $V_{DD}=10\text{V}$ | - | 50 | 100 | ns |
| | | $V_{DD}=15\text{V}$ | - | 40 | 80 | ns |
| input capacitance | C_I | any input | - | 5 | 7.5 | pF |

4、Testing Circuit

4.1、AC Testing Circuit




Figure 3. Test circuit for switching times

Definitions for test circuit:

DUT=Device Under Test.

C_L =Load capacitance including jig and probe capacitance.

R_T =Termination resistance should be equal to the output impedance Z_o of the pulse generator.

4.2、AC Testing Waveforms




Figure 4. Propagation delay, output transition time

4.3、Measurement Points

| Supply voltage | Input | Output |
|----------------|---------------------|---------------------|
| V_{DD} | V_M | V_M |
| 5V to 15V | $0.5 \times V_{DD}$ | $0.5 \times V_{DD}$ |


4.4、Test Data

| Supply voltage | Input | | Load |
|----------------|----------------------|--------------------|-------|
| V_{DD} | V_I | t_r, t_f | C_L |
| 5V to 15V | V_{SS} or V_{DD} | $\leq 20\text{ns}$ | 50pF |



5、Package Information


5.1、DIP14



| Symbol | Dimensions In Millimeters | | Dimensions In Inches | |
|--------|---------------------------|--------|----------------------|-------|
| | Min | Max | Min | Max |
| A | 3.710 | 4.310 | 0.146 | 0.170 |
| A1 | 0.510 | | 0.020 | |
| A2 | 3.200 | 3.600 | 0.126 | 0.142 |
| B | 0.380 | 0.570 | 0.015 | 0.022 |
| B1 | 1.524 (BSC) | | 0.060 (BSC) | |
| C | 0.204 | 0.360 | 0.008 | 0.014 |
| D | 18.800 | 19.200 | 0.740 | 0.756 |
| E | 6.200 | 6.600 | 0.244 | 0.260 |
| E1 | 7.320 | 7.920 | 0.288 | 0.312 |
| e | 2.540 (BSC) | | 0.100 (BSC) | |
| L | 3.000 | 3.600 | 0.118 | 0.142 |
| E2 | 8.400 | 9.000 | 0.331 | 0.354 |




5.2、SOP14






5.3、TSSOP14



| SYMBOL | MILLIMETER | |
|--------|------------|------|
| | MIN | MAX |
| A | — | 1.20 |
| A1 | 0.05 | 0.15 |
| A2 | 0.90 | 1.05 |
| A3 | 0.39 | 0.49 |
| b | 0.20 | 0.30 |
| b1 | 0.19 | 0.25 |
| c | 0.13 | 0.19 |
| c1 | 0.12 | 0.14 |
| D | 4.86 | 5.06 |
| E1 | 4.30 | 4.50 |
| E | 6.20 | 6.60 |
| e | 0.65BSC | |
| L | 0.45 | 0.75 |
| L1 | 1.00BSC | |
| θ | 0 | 8° |



SECTION B-B



6、 Statements And Notes

6.1、 The name and content of Hazardous substances or Elements in the product

| Part name | Hazardous substances or Elements | | | | | | | | | |
|-------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------|-------------------------------|-------------------------------|--------------------------|--------------------------------|-------------------|-----------------------|---------------------------|----------------------|
| | Lead and lead compounds | Mercury and mercury compounds | Cadmium and cadmium compounds | Hexavalent chromium compounds | Polybrominated biphenyls | Polybrominated biphenyl ethers | Dibutyl phthalate | Butylbenzyl phthalate | Di-2-ethylhexyl phthalate | Diisobutyl phthalate |
| Lead frame | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Plastic resin | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Chip | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| The lead | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| Plastic sheet installed | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ | ○ |
| explanation | ○: Indicates that the content of hazardous substances or elements in the detection limit of the following the SJ/T11363-2006 standard. ×: Indicates that the content of hazardous substances or elements exceeding the SJ/T11363-2006 Standard limit requirements. | | | | | | | | | |

6.2、 Notion

Recommended carefully reading this information before the use of this product;

The information in this document are subject to change without notice;

This information is using to the reference only, the company is not responsible for any loss;

The company is not responsible for the any infringement of the third party patents or other rights of the responsibility.