

FH2311A

P-Channel Enhancement Mode MOSFET




<p>Description</p> <p>The FH2311A uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as -2.5V. This device is suitable for use as a wide variety of applications.</p> <p>Applications</p> <ul style="list-style-type: none"> ● PWM Applications ● Load Switch ● Power Management 	<p>Features</p> <ul style="list-style-type: none"> ● $V_{DS} = -17V$; $I_D = -9.0A$ ● $R_{DS(ON)}$ (Typ.)= 16 mΩ @ $V_{GS} = -4.5V$ ● $R_{DS(ON)}$ (Typ.)= 23 mΩ @ $V_{GS} = -2.5V$ ● Low Gate Charge ● High Power and current handing capability ● Lead free product is acquired ● SMD Package(SOT-23) 	
 <p>Schematic diagram</p>	 <p>Marking and Pin Assignment</p>	 <p>SOT-23 top view</p>

Table 1. Absolute Maximum Ratings ($T_A=25^\circ C$ unless otherwise noted)

Symbol	Parameter	Limit	Unit
V_{DS}	Drain-Source Voltage ($V_{GS}=0V$)	-17	V
V_{GS}	Gate-Source Voltage ($V_{DS}=0V$)	± 12	V
I_D	Drain Current-Continuous($T_A=25^\circ C$)	-9	A
	Drain Current-Continuous($T_A=100^\circ C$)	-5.8	A
I_{DM} (pluse)	Drain Current-Continuous@ Current-Pulsed (Note 1)	-36	A
P_D	Maximum Power Dissipation($T_A=25^\circ C$)	1.25	W
	Maximum Power Dissipation($T_A=100^\circ C$)	0.6	W
E_{AS}	Avalanche energy (Note 2)	20	mJ
T_J, T_{STG}	Operating Junction and Storage Temperature Range	-55 To 150	$^\circ C$

Table 2. Thermal Characteristic

Symbol	Parameter	Typ	Max	Unit
$R_{\theta JA}$	Thermal Resistance, Junction-to- Ambient		102	$^\circ C/W$

Table 3. Electrical Characteristics ($T_J=25^\circ\text{C}$ unless otherwise noted)




Symbol	Parameter	Conditions	Min	Typ	Max	Unit
On/Off States						
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=-250\mu A$	-17			V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS}=-17V, V_{GS}=0V, T_J=25^\circ\text{C}$			-1	μA
		$V_{DS}=-17V, V_{GS}=0V, T_J=125^\circ\text{C}$			-100	μA
I_{GSS}	Gate-Body Leakage Current	$V_{GS}=\pm 12V, V_{DS}=0V$			± 100	nA
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=-250\mu A$	-0.5		-1	V
g_{FS}	Forward Transconductance	$V_{DS}=-5V, I_D=-10A$		16.6		S
$R_{DS(ON)}$	Drain-Source On-State Resistance	$V_{GS}=-4.5V, I_D=-5A, T_J=25^\circ\text{C}$		16	21	m Ω
$R_{DS(ON)}$	Drain-Source On-State Resistance	$V_{GS}=-2.5V, I_D=-4A, T_J=25^\circ\text{C}$		23	28	m Ω
Dynamic Characteristics						
C_{iss}	Input Capacitance	$V_{DS}=-10V, V_{GS}=0V, f=1.0\text{MHz}$		1440		pF
C_{oss}	Output Capacitance			294		pF
C_{rss}	Reverse Transfer Capacitance			242		pF
R_g	Gate resistance	$V_{GS}=0V, V_{DS}=0V, f=1.0\text{MHz}$		25		Ω
Switching Parameters						
$t_{d(on)}$	Turn-on Delay Time	$V_{GS}=-10V, V_{DS}=-6V, R_L=2\Omega, R_{GEN}=3\Omega$		14.4		nS
t_r	Turn-on Rise Time			5.5		nS
$t_{d(off)}$	Turn-Off Delay Time			59.4		nS
t_f	Turn-Off Fall Time			21.6		nS
Q_g	Total Gate Charge	$V_{GS}=-4.5V, V_{DS}=-6V, I_D=-5A$		20		nC
Q_{gs}	Gate-Source Charge			5		nC
Q_{gd}	Gate-Drain Charge			6		nC
Source-Drain Diode Characteristics						
I_{SD}	Source-Drain Current (Body Diode)				-9	A
V_{SD}	Forward on Voltage ^(Note 3)	$V_{GS}=0V, I_S=-5A$			-1.2	V
t_{rr}	Reverse Recovery Time	$I_F=-5A, di/dt=-100A/\mu s$		31.2		ns
Q_{rr}	Reverse Recovery Charge	$I_F=-5A, di/dt=-100A/\mu s$		10.9		nC

Notes 1.Repetitive Rating: Pulse width limited by maximum junction temperature.



Notes 2.EAS condition: $T_J=25^\circ\text{C}, V_{DD}=-20V, V_G=-10V, R_g=25\Omega, L=0.5\text{mH}$.

Notes 3.Repetitive Rating: Pulse width limited by maximum junction temperature.


Typical Electrical And Thermal Characteristics (Curves)



Typical Electrical And Thermal Characteristics (Curves)



Package Dimensions : SOT-23



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP.		0.037 TYP.	
e1	1.800	2.000	0.071	0.079
L	0.550 REF.		0.022 REF.	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°