





P . C . B LAYOUT



SPECIFICATION

1. Rating : DC12V 50mA.
2. Contact resistance: $\leq 100\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
4. Withstanding voltage: 250VAC .
5. Operating Force: $400\text{gf} \pm 100$
6. life test: 10,000 cycles.
7. Operation temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
8. Sign"* "is importance dimension.

H=2.5/3.5mm

				TOLERANCE UNLESS SPECIFIED						
				<1.5: $\pm 0.1\text{mm}$ >1.5~5.0: $\pm 0.25\text{mm}$ >5.0: $\pm 0.3\text{mm}$	ANGULAR $\pm 1^{\circ}$	A1				
5	STEM	LCP	1	BALCK		NO	DATE	REVISIONS		BY APPD
4	COVER	PHOSPHOR BRONZE	1	Sn-PLATED	TITLE: TACT SWITCH			UNIT : MM	ROHS COMPLIANT	DWN
3	CONTACT	SUS	1	Ag-PLATED	MODEL: TS-1188U-H			SCALE: 1:1		CHK'D
2	CASE	LCP	1	BLACK						APPD
1	TERMINAL	PHOSPHOR BRONZE	4	Ag-PLATED						
NO.	PART NAME	MATERIAL	QTY	FINISHING						



DONGGUANG HAOYU ELECTRONICS CO., LTD
东莞市弘皓电子有限公司

PRO.AGL: REV :A0