




接触电阻:  $\leq 20\text{M}\Omega$   
 绝缘电阻:  $\geq 1000\text{M}\Omega$   
 插拔力:  $\geq 0.05\text{kg/P}$ ,  $\leq 0.1\text{kg/P}$   
 额定电流: 1A/针  
 环境温度:  $-55^\circ \sim 105^\circ$   
 焊接温度时间:  $\leq 235^\circ$ ,  $\leq 3\text{s}$   
 触点材质: 磷青铜, (连带)镀镍  $\geq 130\mu$   
 绝缘座: PBT  
 耐压: 1000VAC60s,  
 无击穿. 闪络. 飞弧  
 盐雾测试: 24小时不生锈  
 沉降盐雾浓度:  $(5 \pm 1)\% \text{NaCl (m/m)}$   
 试验箱温度:  $(35 \pm 2)^\circ \text{C}$

24P. 28P. 32P=1.70 其它无筋



8P-PCB LAYOUT

规格	A	B	C	D	E
6	5.08 <sup>+0.10</sup> <sub>-0.10</sub>	7.62 <sup>+0.10</sup> <sub>-0.10</sub>	8.20 <sup>+0.20</sup> <sub>-0.20</sub>	7.62 <sup>+0.30</sup> <sub>-0.30</sub>	10.04 <sup>+0.10</sup> <sub>-0.05</sub>
8	7.62 <sup>+0.10</sup> <sub>-0.10</sub>	10.16 <sup>+0.10</sup> <sub>-0.10</sub>			
14	15.24 <sup>+0.10</sup> <sub>-0.10</sub>	17.78 <sup>+0.10</sup> <sub>-0.10</sub>			
16	17.78 <sup>+0.10</sup> <sub>-0.10</sub>	20.32 <sup>+0.10</sup> <sub>-0.10</sub>			
18	20.32 <sup>+0.10</sup> <sub>-0.10</sub>	22.86 <sup>+0.10</sup> <sub>-0.10</sub>			
20	22.86 <sup>+0.10</sup> <sub>-0.10</sub>	25.40 <sup>+0.10</sup> <sub>-0.10</sub>			
24	27.94 <sup>+0.10</sup> <sub>-0.10</sub>	30.48 <sup>+0.10</sup> <sub>-0.10</sub>			
28	33.02 <sup>+0.10</sup> <sub>-0.10</sub>	35.56 <sup>+0.10</sup> <sub>-0.10</sub>			
32	38.10 <sup>+0.10</sup> <sub>-0.10</sub>	40.64 <sup>+0.10</sup> <sub>-0.10</sub>			
			未生产		

ECN BO.		DESCRIPTION.		DATE.	REV.	SCALE: 1/2	SCALE: 3:1
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				
Mikey	Tom	Jerry	PART NAME	H2541FV-C762-2xXXP	UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X.	$\pm 0.25$
			MODEL NAME	H2541FV-C762-2xXXP		X.x	$\pm 0.20$
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx	$\pm 0.15$
						ANGULAIR	$\pm 3$
						FILE.NO.	

瀚源