







## NOTES 备注:

## 1. MATERIAL 材料:

1.1 HOUSING 胶壳: THERMOPLASTIC, HIGH TEMP, UL94V-0, COLOR: BLACK.

1.2 LATCH 锁存器: THERMOPLASTIC, HIGH TEMP, UL94V-0, COLOR: SEE PART NO.

1.3 CONTACTS 端子: COPPER ALLOY.

1.4 HOLD DOWN 压端: COPPER ALLOY.

## 2. FINISH 电镀:


## 2.1 CONTACT 端子:

SELECTIVE GOLD PLATING ON THE CONTACT AREA.  
100u" MIN. MATTE-TIN PLATING ON THE SOLDERING AREA.  
50u" MIN. NICKEL UNDER PLATING OVERALL.

## 2.2 HOLD DOWN 压端:

100u" MIN. MATTE-TIN PLATING ON THE SOLDERING AREA.  
50u" MIN. NICKEL UNDER PLATING OVERALL.


| DIMENSIONS |        |                                     |        |         |         |
|------------|--------|-------------------------------------|--------|---------|---------|
| POSITION   | A±0.20 | B <sup>+0.20</sup> <sub>-0.08</sub> | C±0.25 | D ±0.25 | E ±0.55 |
| 36         | 6      | 7.65                                | 9.15   | 25      | 50.7    |
| 64         | 20     | 21.65                               | 23.15  | 39      | 64.7    |
| 98         | 37     | 38.65                               | 40.15  | 56      | 81.7    |
| 164        | 70     | 71.65                               | 73.15  | 89      | 114.7   |



| DESCRIPTION      | DATE            | REVISED      | APPROVED | UNSPECIFIED TOLERANCES |
|------------------|-----------------|--------------|----------|------------------------|
| REVISIONS        |                 |              |          |                        |
| www.helloxkb.com | www.helloxkb.cn | www.xk-dg.cn |          |                        |

|      |             |                              |
|------|-------------|------------------------------|
| DSND | SCALE: N/A  | MODEL TYPE:                  |
| DWN  | VIEW:       | PART NO.: X1621WVS-XX-9TV15  |
| CHKD | UNIT: mm/in | DWG NO.: X-X1621WVS-XX-9TV15 |
| APPD | SIZE: A4    | WEIGHT                       |
|      |             | SHEET 1/1                    |
|      |             | REVISION A0                  |

XKB INDUSTRIAL PRECISION CO., LIMITED

**X1621 WVS-XX-9TV15**

① ② ③ ④ ⑤ ⑥ ⑦

① Series Number



② Terminal form: W-Wafer

③ Welding Board Angle : V-Stright Angle 180°

④ Welding Way:S-SMT

⑤ No.of Pins: 36~164 Pin

⑥ Plastic material: PA9T/PA46 UL94V-0

⑦ Contact Plating:V15-Gold 15u"  
V30-Gold 30u"

| POS. | DIM. A | DIM. C | DIM. H | "M" |
|------|--------|--------|--------|-----|
| 36   | 6      | 9.15   | 8.15   | B17 |
| 64   | 20     | 23.15  | 22.15  | B31 |
| 98   | 37     | 40.15  | 39.15  | B48 |
| 164  | 70     | 73.15  | 72.15  | B81 |

广东星坤科技股份有限公司

日期  
文件工程章

DESCRIPTION

REVISIONS

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

DATE

REVISED

APPROVED

UNSPECIFIED TOLERANCES

|             |      |
|-------------|------|
| ANGULAR     | ±5°  |
| L ≤ 4       | ±0.2 |
| 4 < L ≤ 16  | ±0.3 |
| 16 < L ≤ 63 | ±0.4 |
| L > 63      | ±0.5 |

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

|      |  |             |                                 |
|------|--|-------------|---------------------------------|
| DSND |  | SCALE: N/A  | MODEL TYPE:                     |
| DWN  |  | VIEW:       | PART NO.:<br>X1621WVS-XX-9TV15  |
| CHKD |  | UNIT: mm/in | DWG NO.:<br>X-X1621WVS-XX-9TV15 |
| APPD |  | SIZE: A4    | WEIGHT<br>SHEET<br>REVISION     |
|      |  |             | 1/1<br>A0                       |