


PCB LAYOUT



Specifications:
 规格:
 1. Voltage rating: 250V AC/DC
 额定电压: 250V AC/DC
 2. Current rating: 3A AC/DC
 额定电流: 3A AC/DC
 3. Withstanding voltage: 500V AC/minute
 耐受电压: ≥500V AC/分钟
 4. Temperature range: -55°C~+105°C
 温度范围: -55°C~+105°C
 5. Insulation resistance: 1000MΩMIN
 绝缘电阻: ≥1000MΩ
 6. Contact resistance: 30mΩMax
 接触电阻: ≥30mΩ
Material:
 材料:
 7. Rubber core: PBT UL94V-0
 胶芯: PBT UL94V-0
 8. The iron shell: SPCC Nivkel Plating/Tin Plating/Gold Plating
 铁壳: SPCC, 镀镍/镀锡/镀金
 B、成品不能有弯针, R角不一致等不良。

X05 XX W X X X X
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series NO.
- ② Row No. Pin No. XX-15;26;44;62
- ③ Welding Board Angle :W-Male
- ④ T; Traditonal C: Car-pin
- ⑤ Planting Category: 1:1U 2:2U 3:3U 4:5U 5:15U 6:30U 7:AuSn
- ⑥ Color: B-BLACK W-White BL-Blue
- ⑦ 1:TYPE-1; 2:TYPE-2; 5:TYPE-5; 7:TYPE-7

NUMBER OF POSITIONS	DIMENSION			
	A±0.25	B±0.13	C±0.38	D±0.25
15	18.00	24.99	30.80	19.28
26	26.50	33.32	39.20	27.51
44	40.00	47.04	53.50	41.28
62	56.60	63.50	69.40	57.71

铆合方式	TYPE-1: 铆合	TYPE-2: 前铆实心螺母	TYPE-7: 后铆鱼叉	TYPE-5: 铆鱼叉锁螺丝
图示				

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



DSND	SCALE: N/A	MODEL TYPE: D-USB
DWN	VIEW:	PART NO.: X05XXWXXXX
CHKD	UNIT: mm/in	DWG NO.: X-X05XXWXXXX
APPD	SIZE: A4	WEIGHT SHEET REVISION
		1/1 A0