

SUGGESTED PCB LAYOUT  
(COMPONENT SIDE)

孔位	A-(mm)	B-(mm)	C-(mm)
2P	1.25	7.5	—
3P	2.50	8.75	—
4P	3.75	10.00	2.50
5P	5.00	11.25	3.75
6P	6.25	12.50	5.00
7P	7.50	13.75	6.25
8P	8.75	15.00	7.50
9P	10.00	16.25	8.75
10P	11.25	17.50	10.00
11P	12.50	18.75	11.25
12P	13.75	20.00	12.50
13P	15.00	21.25	13.75
14P	16.25	22.50	15.00
.....	....	.....	.....
20P	23.75	30.15	22.50

技术要求


1: 外观要求

- 1-1. 插针表面光洁、无损伤、锈蚀等缺陷。
- 1-2. 基座表面无脏污、飞边、排气不良等缺陷。

2: 电气性能:

- 2-1. 额定电流: 1.0A
- 2-2. 额定电压: 125V
- 2-3. 耐电压: 250V
- 2-4. 接触电阻: ≤20mΩ
- 2-5. 绝缘电阻: ≥100mΩ

3: 工作温度: -25℃~+85℃



new		2015/5/3		A		瀚源
ECN BO.		DESCRIPTION.		DATE.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER	SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	9827WRS-XXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:	X.           ±0.25
			MODEL NAME	9827WRS-XXP		X.x          ±0.20
			3RD ANGLE PROJ	HanElectricity Co.,LTD		
				HanElectricity Co.,LTD		FILE.NO.