



MUR3060PTS

Superfast Recovery Rectifiers

Features

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ Construction utilizes void-free molded plastic technique
- ◆ Low reverse leakage
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed
260°C/10 seconds at terminals


Mechanical Data

Case : Molded plastic body

Terminals : Solder plated, solderable per MIL-STD-750, Method 2026

Polarity : Polarity symbol marking on body

Mounting Position : Any



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified. Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	MUR 3005PTS	MUR 3010PTS	MUR 3020PTS	MUR 3040PTS	MUR 3050PTS	MUR 3060PTS	UNITS
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	500	600	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	350	420	V
Maximum DC blocking voltage	V _{DC}	50	100	200	400	500	600	V
Maximum average forward rectified current at T _c =110°C per device per diode	I _(AV)	30.0 15.0						A
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load	I _{FSM}	200.0						A
Maximum instantaneous forward voltage per diode at 15.0A	V _F	1.0			1.4	2.2		V
Maximum DC reverse current at rated DC blocking voltage T _A =25°C T _A =125°C	I _R	10 500						u A
Maximum reverse recovery time	T _{rr}	35						ns
Typical thermal resistance	R _{qjc}	3.5						°C/W
Operating junction temperature range	T _J	-55 to +150						°C
Storage temperature range	T _{STG}	-55 to +150						°C

Note: 1. Reverse recovery time test condition: $I_F=0.5\text{A}$ $I_R=1.0\text{A}$ $I_{rr}=0.25\text{A}$



MUR3005PTS-MUR3060PTS

Superfast Recovery Rectifiers

Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted)

FIG. 1- DERATING CURVE OUTPUT RECTIFIED CURRENT




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PER LEG




FIG. 3-TYPICAL FORWARD VOLTAGE CHARACTERISTICS




FIG. 4-TYPICAL REVERSE LEAKAGE CHARACTERISTICS

