


芯数 Pin	额定电流 Rate Current	额定电压 Rate Voltage	耐压 Dielectric Withstanding Voltage
4	4A	250V	1500 V/Min
5	4A	250V	1200 V/Min
8	2A	30V	500 V/Min
12	1A	30V	500 V/Min

材料Material
 胶芯原料Insulator: PA46, (UL 94V-0)
 外壳材料Related Material: Brass
 表面涂层Surface Coating: Nickel Plating
 针材料Related Material: Male-Brass
 Female-Bronze

表面涂层Surface Coating: Overgold 1u
 规格参数Planning Parameters
 绝缘电阻Insulation Resistance: $\geq 100M\Omega$
 工作温度Operating Temperature: $-40+150^\circ$



上海洲日电子有限公司

Shanghai Zhouri Electronics CO.,LTD

上海康司玛电子设备进出口有限公司

Shanghai KangSiMa Electronic Equipment
 Import and export Co.,LTD

tel: 021-51571121
 fax: 021-51571120

<http://www.zhouri.net>

产品名称: M12-A-XP-M-BH1-HX

绘图: MAXIA	日期: 202111027
审核: 张海娜	日期: 202111027
版本编号: ZRLCGY2021-10-20-CJ/1	
第三视角:	单位: mm

比例: 图幅: A4 页次 共 01 第 01