






Electrical schematic diagram without lights
无灯电气原理图



Installation View
安装视图

A4				 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP93002P1S
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROC CPU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basis of manufacture or sale of apparatus without permission				

A		B		C		D		E		F		G	
1	性能参数												
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A						13. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃						
	2. Rated current:3A/DC36V 额定电流:3A/DC36V						14. Compression torque: ≤ 3.5N 按压扭力: ≤3.5N						
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min						15. Electrical life: 100000 cycles 电气寿命: 100000 cycles						
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ						16. mechanical: 500000cycles 机械寿命: 500000cycles						
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ						17. Operation method:Self-locking type 操作方式: 自锁式						
	6. Pressing stroke:3.00mm ± 0.10 按压行程:3.00mm ± 0.10						18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10												
	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃												
	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration												
	10. Nut assembly torque:5-14N 螺帽装配力矩:5-14N												
	11. Protection level:IP67 防护等级:IP67												
2	12. Explosion prevention level: IK10 防暴等级: IK10												
	连接形式												
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下												
	2. Can be used with dedicated connectors: 可配专用接插件使用:												
	2.1 1NO2NCSwitch function wire: green (C) blue wire (NO) yellow wire (NC) 1NO2NC开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)												
	2.2 2NO2NC switch function wire: green black wire c, blue black wire NO, yellow white wire NC 2NO2NC开关功能线材: 绿黑线 (C) 蓝黑线 (NO)、黄白先(NC)												

A		B		C		D		E		F		G	
材质参数													
8		Base 底座		PA46		1							
7		Pin 引脚		Brass 黄铜		1				gold-plating 镀金			
6		Contact material 接触材质		silver alloy 银合金		1				Silvering 镀银			
5		LED Base LED基座		PC 塑胶		1							
4		Arm nut 固定螺帽		Brass 黄铜		1				nickeling 镀镍			
3		Oring O型圈		Silica gel 硅胶		1							
2		Housing 外壳		SUS 不锈钢		1							
1		Key 按键		SUS 不锈钢		1							
NO 序号		Part name 部件名		Material 材料		QTY 数量				Remark 备注			

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP93002P1S
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE						
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				