




A4				 台普 ROC PU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91909P1A
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROC PU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	—	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				

A				B		C		D		E		F		G								
1	性能参数															1						
	1. Heating current: Ui: AC250V, Ith: 5A 发热电流: Ui: AC250V, Ith: 5A					13. Electrical life: 500000 cycles 电气寿命: 500000 cycles																
	2. Rated current:3A/DC36V 额定电流:3A/DC36V					14. mechanical: 500000cycles 机械寿命: 500000cycles																
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min					15. Operation method:Self-locking type 操作方式: 自锁式																
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ					16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N																
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ																					
	6. Pressing stroke:3.00mm ± 0.10 按压行程:3.00mm ± 0.10																					
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10																					
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N																					
	9. Protection level:IP67 防护等级:IP67																					
2																2						
	10. Explosion prevention level: IK10 防暴等级: IK10																					
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃																					
	12. Compression torque: ≤ 6N 按压扭力: ≤6N																					
	连接形式																4					
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下																					
	2. Can be used with dedicated connectors: 可配专用接插件使用:																					
	2.1 1NO1NCSwitch function wire: Green Line (C), blue Line (NO), yellow Line (NC) 1NO1NC开关功能线材: 绿线(C)、蓝线(NO)、黄线(NC)																					
	2.2 NO2NC switch function wire: green black wire (C), blue black wire (NO), yellow white wire (NC) 2NO2NC开关功能线材: 绿黑线(C)、蓝黑线(NO)、黄白线(NC)																					
3																3						
4																4						
5																5						
A4															 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3																		DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91909P1A
A2																X.XX ± 0.10		DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1																X.X ± 0.15		ROC CPU TECHNOLOGY CO.,LTD				
REV																X ± 0.25						
															ANGULAR		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
A				B		C		D		E		F		G								

	A	B	C	D	E	F	G
1	材质参数						1
2	8	Base 底座	PA46	1			
	7	Pin 引脚	Brass 黄铜	1		gold-plating 镀金	2
	6	Contact material 接触材质	silver alloy 银合金	1		Silvering 镀银	
	5	LED Base LED基座	PC 塑料	1			
3	4	Arm nut 固定螺帽	Brass 黄铜	1		nickeling 镀镍	3
	3	Oring O型圈	Silica gel 硅胶	1			
	2	Housing 外壳	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色	
4	1	Key 按键	Aluminum alloy 铝合金	1		Oxidized/Black 氧化/黑色	4
	NO 序号	Part name 部件名	Material 材料	QTY 数量		Remark 备注	

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91909P1A
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					

A	B	C	D	E	F	G
---	---	---	---	---	---	---

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission