

## Features

- Transient protection for high-speed data lines  
IEC 61000-4-2 (ESD) ±25kV (Air)  
±20kV (Contact)
- Cable Discharge Event (CDE)
- Package optimized for high-speed lines
- Ultra-small package (1.0mm×0.6mm×0.55mm)
- Protects one data, control or power line
- Low capacitance: 0.35pF (Typical)
- Low leakage current: 10nA @ V<sub>RWM</sub> (Typical)
- Low clamping voltage
- Each I/O pin can withstand over 1000 ESD strikes for ±8kV contact discharge
- ROHS compliant

## Description

TT0501SBX is a low -capacitance Transient Voltage Suppressor (TVS) designed to provide electrostatic discharge (ESD) protection for high-speed data interfaces. With typical capacitance of 0.35pF only, TT0501SBX is designed to protect parasitic - sensitive systems against over-voltage and over-current transient events. It complies with IEC 61000-4-2 (ESD), Level 4 ( $\pm 15\text{kV}$  air,  $\pm 8\text{kV}$  contact discharge), very fast charged device model (CDM) ESD and cable discharge event (CDE), etc.

TT0501SBX uses ultra-small DFN1006-2L package. Each TT0501SBX device can protect one high -speed data line. It offers system designers flexibility to protect single data line where space is a premium concern. The combined features of low capacitance, ultra-small size and high ESD robustness make TT0501SB ideal for high-speed data port and high -frequency line (e.g., USB 2.0 & antenna line) applications, such as cellular phones and HD visual devices.


## Applications

- Serial ATA
- PCI Express
- Desktops, Servers and Notebooks
- Cellular Phones
- MDDI Ports
- USB2.0/3.0 Power and Data Line Protection
- Display Ports
- Digital Visual Interfaces (DVI)
- HDMI 1.4/2.0


## Mechanical Characteristics

- DFN1006-2L package
- Flammability Rating: UL 94V-0
- Packaging: Tape and Reel

## Circuit Diagram



## Pin Configuration




DFN1006-2L  
(Top View)

## Absolute Maximum Rating

Symbol	Parameter	Value	Units
P <sub>PK</sub>	Peak Pulse Power (8/20μs)	40	W
I <sub>PP</sub>	Peak Pulse Current(tp=8/20us)	4	A
V <sub>ESD</sub>	ESD per IEC 61000-4-2(Air) ESD per IEC 61000-4-2 (Contact)	±25 ±20	kV
T <sub>OPT</sub>	Operating Temperature	-55/+125	°C
T <sub>STG</sub>	Storage Temperature	-55/+150	°C

## Electrical Characteristics (T = 25°C)


Symbol	Parameter
V <sub>RWM</sub>	Nominal Reverse Working Voltage
I <sub>R</sub>	Reverse Leakage Current @ V <sub>RWM</sub>
V <sub>BR</sub>	Reverse Breakdown Voltage @ I <sub>T</sub>
I <sub>T</sub>	Test Current for Reverse Breakdown
V <sub>C</sub>	Clamping Voltage @ I <sub>PP</sub>
I <sub>PP</sub>	Peak Pulse Current
C <sub>ESD</sub>	Parasitic Capacitance
V <sub>R</sub>	Reverse Voltage
f	Small Signal Frequency




Symbol	Test Condition	Minimum	Typical	Maximum	Units
V <sub>RWM</sub>				5.0	V
I <sub>R</sub>	V <sub>RWM</sub> = 5V, T = 25°C Between I/O and I/O		0.01	0.1	µA
V <sub>BR</sub>	I <sub>T</sub> = 1mA Between I/O and I/O	6.0	8.0		V
V <sub>C</sub>	I <sub>PP</sub> = 1A, t <sub>p</sub> = 8/20µs Between I/O and I/O		9.6	12.0	V
	I <sub>PP</sub> = 4A, t <sub>p</sub> = 8/20µs Between I/O and I/O		13.0	15.0	V
V <sub>C</sub>	I <sub>PP</sub> = 8.0A, t <sub>p</sub> = 100ns <sup>(1)</sup>		14.5		V
	I <sub>PP</sub> = 16.0A, t <sub>p</sub> = 100ns <sup>(1)</sup>		18.5		V
R <sub>dyn</sub>	I <sub>PP</sub> = 34.0A, t <sub>p</sub> = 322ps <sup>(1)</sup>		0.7		Ω
C <sub>ESD</sub>	V <sub>R</sub> = 0V, f = 1MHz Between I/O and I/O		0.35		pF

Notes:(1)Measurements performed using a 100ns Transmission Line Pulse(TLP) system.

### Voltage Sweeping of I/O to I/O




### TLP Measurement of I/O to I/O




### Capacitance vs. Voltage of I/O to I/O ( $f = 1\text{MHz}$ )

Capacitance vs. Reverse Voltage




Normalized Capacitance vs. Reverse Voltage



## Recommended Soldering Conditions

### Reflow Soldering




### Recommended Conditions

Profile Feature	Pb-Free Assembly
Average ramp-up rate ( $T_L$ to $T_P$ )	3°C/second max.
Preheat -Temperature Min ( $T_{S \text{ min}}$ ) -Temperature Max ( $T_{S \text{ max}}$ ) -Time (min to max) ( $t_s$ )	150°C 200°C 60-180 seconds
$T_{S \text{ max}}$ to $T_L$ -Ramp-up Rate	3°C/second max.
Time maintained above: -Temperature ( $T_L$ ) -Time ( $t_L$ )	217°C 60-150 seconds
Peak Temperature ( $T_P$ )	260°C
Time within 5°C of actual Peak Temperature ( $t_P$ )	20-40 seconds
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8 minutes max.

## Package Outline


- DFN1006-2L Package
- MSL-1



Package Dimensions (Controlling dimensions are in millimeters)

Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Minimum	Maximum	Minimum	Maximum
A	0.400	0.550	0.016	0.022
A1	0.000	0.050	0.000	0.002
A3	0.125 REF		0.005 REF	
D	0.950	1.050	0.037	0.041
E	0.550	0.650	0.022	0.026
b	0.200	0.300	0.008	0.012
e	0.650 BSC		0.026 BSC	
L	0.450	0.550	0.018	0.022

## Tape and Reel Specification



Symbol	W	A0	B0	K0	E	F	P	P0	P2	T
Dimensions (mm)	$8.00 \pm 0.1$	$0.7 \pm 0.05$	$1.15 \pm 0.05$	$0.55 \pm 0.05$	$1.75 \pm 0.1$	$3.5 \pm 0.05$	$2.0 \pm 0.1$	$4.0 \pm 0.1$	$2.0 \pm 0.05$	$0.2 \pm 0.05$

## Marking Codes

S

Or

2B

### Note:

- (1) "S" is part number , fixed .

### Note:

- (1) "2B" is part number, fixed .

## Ordering Information

Part Number	Working Voltage	Quantity Per Reel	Reel Size
TT0501SBX	5V	10,000	7 Inch