








P.C.B LAYOUT



SCHEMATIC



SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $200\pm 100gf$.
- 6.Travel: $0.25\pm 0.1mm$.
- 7.life test: 100,000 cycles.
- 8.Operation temperature range: $-25^{\circ}C\sim 85^{\circ}C$.
- 9.Sign"* "is importance dimension.

高度	
H=4.5mm	✓
H=5.0mm	
H=5.5mm	
H=6.0mm	
H=7.0mm	
H=7.5mm	
H=8.0mm	
H=9.0mm	
H=(10 - 27)mm	

脚距 L	
8.0 mm	
8.8 mm	
9.8 mm	

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°							
5	KNOB	PA9T	1	BLACK/RED			NO	DATE	REVISIONS			BY	APPD
4	COVER	BRASS/SUS	1	Sn-PLating	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
3	CONTACT	SUS	1	Ag-Plated	MODEL: TC-06104-045E				SCALE: 1:1	COMPLIANT	CHK'D		
2	CASE	PA9T	1	BLACK	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD				
1	TERMINAL	BRASS	1	Ag-Plated									
NO.	PART NAME	MATERIAL	QTY	FINISHING							PRO.AGL:		REV :A0