




N-Channel Trench Power MOSFET

<p>General Description</p> <p>The JY2312X uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as 2.5V. This device is suitable for use as a battery protection or in other switching application.</p> <p>Features</p> <ul style="list-style-type: none"> ● $V_{DS} = 20V, I_D = 6A$ ● $R_{DS(ON)} < 26m\Omega @ V_{GS} = 4.5V$ ● $R_{DS(ON)} < 34m\Omega @ V_{GS} = 2.5V$ ● High Power and current handing capability ● Lead free product is acquired ● Surface Mount Package <p>Application</p> <ul style="list-style-type: none"> ● Battery protection ● Load switch ● Power management 	 <p>Schematic Diagram</p>  <p>Marking and pin Assignment</p>  <p>SOT23 top view</p>
--	--

Package Marking and Ordering Information

Device Marking	Device	Device Package	Reel Size	Tape width	Quantity
2312	JY2312X	SOT23	Ø180mm	8mm	3000 units

Table 1. Absolute Maximum Ratings ($T_A=25^\circ C$)

Symbol	Parameter	Value	Unit
V_{DS}	Drain-Source Voltage ($V_{GS}=0V$)	20	V
V_{GS}	Gate-Source Voltage ($V_{DS}=0V$)	± 12	V
I_D	Drain Current-Continuous	6	A
I_{DM} (pulse)	Drain Current-Continuous@ Current-Pulsed (Note 1)	16	A
P_D	Maximum Power Dissipation	1.3	W
T_J, T_{STG}	Operating Junction and Storage Temperature Range	-55 To 150	°C

Notes 1.Repetitive Rating: Pulse width limited by maximum junction temperature

Table 2. Thermal Characteristic

Symbol	Parameter	Value	Unit
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	96	°C/W

Table 3. Electrical Characteristics ($T_A=25^\circ C$ unless otherwise noted)

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
On/Off States						
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	20	22		V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS}=20V, V_{GS}=0V$			1	μA
I_{GSS}	Gate-Body Leakage Current	$V_{GS}=\pm 12V, V_{DS}=0V$			± 100	nA
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\mu A$	0.5	0.7	1.1	V
g_{FS}	Forward Transconductance	$V_{DS}=5V, I_D=5A$	4	8		S
$R_{DS(on)}$	Drain-Source On-State Resistance	$V_{GS}=4.5V, I_D=5A$		18	26	$m\Omega$
		$V_{GS}=2.5V, I_D=4A$		23	34	$m\Omega$
Dynamic Characteristics						
C_{iss}	Input Capacitance	$V_{DS}=10V, V_{GS}=0V, f=1.0MHz$		500		pF
C_{oss}	Output Capacitance			300		pF
C_{rss}	Reverse Transfer Capacitance			140		pF
Switching Times						
$t_{d(on)}$	Turn-on Delay Time	$V_{DD}=10V, I_D=1A, R_L=2.8\Omega$ $V_{GS}=4.5V, R_G=6\Omega$		20		nS
t_r	Turn-on Rise Time			19		nS
$t_{d(off)}$	Turn-Off Delay Time			65		nS
t_f	Turn-Off Fall Time			25		nS
Q_g	Total Gate Charge	$V_{DS}=10V, I_D=5A, V_{GS}=4.5V$		10		nC
Q_{gs}	Gate-Source Charge			2.3		nC
Q_{gd}	Gate-Drain Charge			2.9		nC
Source-Drain Diode Characteristics						
I_{SD}	Source-Drain Current(Body Diode)				5	A
V_{SD}	Forward on Voltage ^(Note 1)	$V_{GS}=0V, I_S=5A$			1.2	V

Notes 1. Repetitive Rating: Pulse width limited by maximum junction temperature.






Switch Time Test Circuit and Switching Waveforms:

TYPICAL ELECTRICAL AND THERMAL CHARACTERISTICS (Curves)
Figure1. Power Dissipation

Figure2. Drain Current

Figure3. Output Characteristics

Figure4. Transfer Characteristics










Figure5. Capacitance

Figure6. $R_{DS(ON)}$ vs Junction Temperature

Figure7. Max BV_{DSS} vs Junction Temperature

Figure8. $V_{GS(th)}$ vs Junction Temperature

Figure9. Gate Charge Waveforms

Figure10. Maximum Safe Operating Area


Figure11. Normalized Maximum Transient Thermal Impedance



SOT23 Package Information



Carrier Dimensions

PKG TYPE	W	P	E	F	D	D1	Po	Po10	P2
SOT23	8.00	4.00	1.75	3.50	1.50	1.00	4.00	40.00	2.00
Tolerance	+0.3/-0.1	± 0.1	± 0.2	± 0.05					

A0	B0	K0	T
3.15	2.77	1.22	0.20
± 0.1	± 0.1	± 0.1	± 0.02

