

MSKSEMI 美森科

SEMICONDUCTOR



ESD



TVS



TSS



MOV



GDT



PLED

MS16N65S

Product specification

Description

The MS16N65S uses advanced trench technology to provide excellent RDS(ON), low gate charge and operation with gate voltages as low as 4.5V. This device is suitable for use as a Battery protection or in other Switching application.




General Features

- $V_{DS} = 650V$ $I_D = 16A$
- $R_{DS(ON)} < 0.55\Omega$ @ $V_{GS} = 10V$

Application

- Battery protection
- Load switch
- Uninterruptible power supply

Reference News

PACKAGE OUTLINE	N-Channel MOSFET	Marking
		
TO-263		MS16N65S

Note : ****Representative production cycle

Absolute Maximum Ratings

Symbol	Parameter	Limit	Units
V_{DS}	Drain-Source Voltage	650	V
V_{GS}	Gate-Source Voltage	± 30	V
I_D	Drain Current-Continuous	16	A
I_{DM}	Drain Current-Pulsed ^a	64	A
P_D	Maximum Power Dissipation @ $T_C = 25^\circ C$ - Derate above $25^\circ C$	180	W
		1.1	W/ C
EAS	Single Pulsed Avalanche Energy ^d	1000	mJ
IAS	Single Pulsed Avalanche Current ^d	64	A
T_J, T_{stg}	Operating and Store Temperature Range	-55 to 175	$^\circ C$
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	0.69	$^\circ C/W$
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	62.5	$^\circ C/W$

Electrical Characteristics $T_C = 25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Min.	Typ.	Max.	Unit	Test Conditions
BV_{DSS}	Drain-to-Source Breakdown Voltage	650	--	--	V	$V_{GS}=0V, I_D=250\mu A$
I_{DSS}	Drain-to-Source Leakage Current	--	--	1.0	uA	$V_{DS}=650V, V_{GS}=0V$
		--	--	100		$V_{DS}=520V, V_{GS}=0V, T_J=125^\circ C$
I_{GSS}	Gate-to-Source Leakage Current	--	--	+100	nA	$V_{GS}=+30V, V_{DS}=0V$
		--	--	-100		$V_{GS}=-30V, V_{DS}=0V$
$R_{DS(ON)}$	Static Drain-to-Source On-Resistance ^[4]	--	0.45	0.55	Ω	$V_{GS}=10V, I_D=8A$
$V_{GS(TH)}$	Gate Threshold Voltage	2.0	--	4.0	V	$V_{DS}=V_{GS}, I_D=250\mu A$
g_{fs}	Forward Transconductance ^[4]	--	15	--	S	$V_{DS}=15V, I_D=8A$
C_{iss}	Input Capacitance	--	2442	--	pF	$V_{GS}=0V, V_{DS}=25V, f=1.0MHz$
C_{rss}	Reverse Transfer Capacitance	--	18.5	--		
C_{oss}	Output Capacitance	--	218	--		
Q_g	Total Gate Charge	--	54	--	nC	$V_{DD}=325V, I_D=16A, V_{GS}=0 \text{ to } 10V$
Q_{gs}	Gate-to-Source Charge	--	12	--		
Q_{gd}	Gate-to-Drain (Miller) Charge	--	21	--		
$t_{d(ON)}$	Turn-on Delay Time	--	15	--	nS	$V_{DD}=325V, I_D=16A, V_{GS}=10V, R_G=6.1\Omega$
t_{rise}	Rise Time	--	52	--		
$t_{d(OFF)}$	Turn-Off Delay Time	--	59	--		
t_{fall}	Fall Time	--	72	--		
I_{SD}	Continuous Source Current ^[4]	--	--	16	A	Integral PN-diode in MOSFET
I_{SM}	Pulsed Source Current ^[4]	--	--	64		
V_{SD}	Diode Forward Voltage	--	--	1.5	V	$I_S=16A, V_{GS}=0V$
t_{rr}	Reverse recovery time	--	380	--	V	$V_{GS}=0V, I_F=16A, di_F/dt=100A/\mu s$
Q_{rr}	Reverse recovery charge	--	2.6	--	uC	

Note:

 [1] $T_J=+25^\circ C$ to $+150^\circ C$

[2] Repetitive rating; pulse width limited by maximum junction temperature.

 [3] $I_{SD} = 16A di/dt < 100 A/\mu s, V_{DD} < BV_{DSS}, T_J=+150^\circ C$.

 [4] Pulse width $\leq 380\mu s$; duty cycle $\leq 2\%$.

Typical Characteristics




Figure 1 Maximum Forward Bias Safe Operating Area




Figure 2 Maximum Power Dissipation vs Case Temperature




Figure 3 Maximum Continuous Drain Current vs Case Temperature




Figure 4 Typical Output Characteristics




Figure 5 Maximum Effective Thermal Impedance, Junction to Case




Figure 6 Maximum Peak Current Capability




Figure 7 Typical Transfer Characteristics




Figure 8 Typical Drain to Source ON Resistance vs Gate Voltage




Figure 9 Typical Drain to Source ON Resistance vs Drain Current




Figure 10 Typical Drain to Source on Resistance vs Junction Temperature




Figure 11 Typical Theshold Voltage vs Junction Temperature




Figure 12 Typical Breakdown Voltage vs Junction Temperature




Figure 13 Typical Capacitance vs Drain to Source Voltage




Figure 14 Typical Gate Charge vs Gate to Source Voltage




Figure 15 Typical Body Diode Transfer Characteristics




Figure 16 Unclamped Inductive Switching Capability

Test Circuits and Waveforms




Fig. 1.1 Peak Diode Recovery dv/dt Test Circuit




Fig. 1.2 Peak Diode Recovery dv/dt Waveforms

Test Circuits and Waveforms (Cont.)




Fig. 2.1 Switching Test Circuit




Fig. 2.2 Switching Waveforms




Fig. 3.1 Gate Charge Test Circuit




Fig. 3.2 Gate Charge Waveform




Fig. 4.1 Unclamped Inductive Switching Test Circuit





Fig. 4.2 Unclamped Inductive Switching Waveforms

TO-263 Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	4.	4.	0.	0.184
A1	4700.	6700.	1760.	0.006
B	0001.	1501.	0000.	0.056
b	1200.	4200.	0440.	0.036
b1	7101.	9101.	0280.	0.054
c	1700.	3700.	0460.	0.021
c1	3101.	5301.	0120.	0.054
D	10700	10370	00464	0.406
E	8.500	8.900	0.335	0.350
e	2.540 TYP.		0.100 TYP.	
e1	4.980	5.180	0.196	0.204
L	14.940	15.500	0.588	0.610
L1	4.	5.	0.	0.215
L2	9502.	4502.	1950.	0.108
L3	3401.	7401.	0920.	0.067
Φ	300	700	051	8°
V	0° 5.600 REF. 8°		0° 0.220REF.	

REEL SPECIFICATION

P/N	PKG	QTY
MS16N65S	TO-263	800

Attention

- Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.
- MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all MSKSEMI Semiconductor products described or contained herein.
- Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- MSKSEMI Semiconductor strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the MSKSEMI Semiconductor product that you intend to use.