



修 订	标 记	修 改 描 要	签 名	日 期
REV A0		NEW DRG		2016-03-12



- Specification:
- 1.Electrical Characteristics:
Contact Current Rating: 3 Amperes Max.
Rated Voltage: 30V Max.
Dielectric Withstanding Voltage: AC 100V r.m.s.
Insulation Resistance: 100 MΩ Minimum.
Contact Resistance: 40 mΩ Maximum.
 - 2.Environmental:
Operating Temperature: -40°C~+85°C.
 - 3.Mechanical Characteristics:
Insertion Force: 5~20Nf.
Withdrawal Force: 6~20Nf.
Durability Cycles: 5000 Cycles.
 4. ☒ Make is FAI test Dimension
▼ Make is major test Dimension



A5	CC1	B5	CC2
A9	VBUS	B9	VBUS
A12	GND	B12	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

		深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话: 0755-27111216 传真: 0755-29940187						
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			 		TITLE: TYPE C 6P立插无弹不锈钢 产品名称: H=6.8贴麦拉			
X. X	±0.30	X. X°	±3°	APPD: 核准:	PART NO: 产品编号: HDGCYLSY-TYPE C-102			
X. XX	±0.20	X. XX°	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X. XXX	±0.10	X. XXX°	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001