




SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100\text{m}\Omega$.
- 3.Insulation resistance: $\geq 100\text{M}\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: $160\pm 50\text{gf}/250\pm 80\text{gf}$
- 6.Travel: $0.25\pm 0.1\text{mm}$.
- 7.life test: 10,000 cycles.
- 8.Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
- 9.Sign"* "is importance dimension.



CIRCUIT DIAGRAM



P . C . B LAYOUT

					TOLERANCE UNLESS SPECIFIED								
					<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	A1 NO	2023.2.17 DATE	更新图纸 REVISIONS		WM BY		
1	TERMINAL	BRASS	1	Ag-PLATED									
2	CASE	PA9T	1	BLACK	TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
3	CONTACT	SUS301	1	Ag-PLATED	MODEL: TC-00104-060E-01				SCALE: 1:1	COMPLIANT	CHK'D		
4	COVER	BRASS	1	Sn-PLATED	 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司				APPD				
5	KNOB	PA9T	1	BLACK									
NO.	PART NAME	MATERIAL	QTY	FINISHING					PRO.AGL: 		REV :A1		